

# UBE - Marker carriers



0800310

<https://www.phoenixcontact.com/gb/products/0800310>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Terminal strip marker carriers for marking terminal groups, for end bracket E/UK or end clamp E/U, lettering field size: 40 x 17 mm

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 0800310             |
| Packing unit                         | 10 pc               |
| Minimum order quantity               | 10 pc               |
| Sales key                            | BG211A              |
| Product key                          | BG211A              |
| Catalog page                         | Page 542 (C-3-2019) |
| GTIN                                 | 4017918005917       |
| Weight per piece (including packing) | 6.58 g              |
| Weight per piece (excluding packing) | 4.685 g             |
| Customs tariff number                | 39269097            |
| Country of origin                    | DE                  |

## Technical data

### Product properties

|              |                 |
|--------------|-----------------|
| Product type | Marker carriers |
|--------------|-----------------|

### Dimensions

|        |         |
|--------|---------|
| Width  | 20 mm   |
| Length | 41.4 mm |

### Text field

|                   |         |
|-------------------|---------|
| Text field width  | 41.4 mm |
| Text field height | 20 mm   |

### Material specifications

|                                        |                                |
|----------------------------------------|--------------------------------|
| Color                                  | gray (RAL 7042)                |
| Material                               | PA                             |
| Flammability rating according to UL 94 | V2                             |
| Components                             | free from silicone and halogen |

### Environmental and real-life conditions

#### Ambient conditions

|                                                     |                   |
|-----------------------------------------------------|-------------------|
| Ambient temperature (operation)                     | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C             |
| Recommended humidity (storage/transport)            | 50 %              |

### Mounting

|               |          |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

# UBE - Marker carriers



0800310

<https://www.phoenixcontact.com/gb/products/0800310>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281105 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002248 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# UBE - Marker carriers



0800310  
<https://www.phoenixcontact.com/gb/products/0800310>

## Environmental product compliance

|                                         |                            |
|-----------------------------------------|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)