

Light-duty protective gloves, offering moderate defenses against chemical hazards

- **Heightened protection:** Made from a special natural rubber latex and neoprene blend, AlphaTec® 87-600 light-duty protective gloves combine strength and elasticity while protecting against hazardous substances
- **Assured tactile sensitivity:** Just 0.43mm/17 mil thick, these thin work gloves ensure excellent tactile sensitivity and dexterity, making it easy to perform delicate light-duty tasks
- **Increased cleanliness:** In addition, AlphaTec® 87-600 neoprene-rubber gloves undergo a surface chlorination treatment, resulting in greater cleanliness and fewer allergy risks

Industries

- Agriculture
- Automotive
- Construction
- Chemical
- Metal fabrication

Applications

- Janitorial use
- Maintenance of plant and machines
- Chemical Handling
- Assembling and mounting components



Previously known as: Duzmor Plus 87-600

Key Features

- **Natural rubber latex and neoprene blend:** Moderate chemical protection
- **0.43mm/17 mil thickness:** For tactile, dexterous hand protection
- **Chlorinated surface:** Enhanced cleanliness and fewer allergy risks

Vulcanization Chemical Accelerators

- Natural rubber proteins
- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.



Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 87-600	Coating Material: Natural Rubber Latex and Neoprene Blend	6.5 - 7, 7.5 - 8, 8.5 - 9, 9.5 - 10	305 / 12	Natural	12 pairs per bag, 12 bags per carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.