

WP-STEEL PVC C 17 - Protective hose

3240869

<https://www.phoenixcontact.com/gb/products/3240869>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective hose, material: Steel, galvanized / PVC, degree of protection: IP68, color: black, inner diameter: 13 mm, Total length: 10 m

Commercial data

Item number	3240869
Packing unit	10 m
Minimum order quantity	10 m
Sales key	BF7DSA
Product key	BF7DSA
Catalog page	Page 600 (C-3-2019)
GTIN	4046356737241
Weight per piece (including packing)	999.9 g
Weight per piece (excluding packing)	999.9 g
Customs tariff number	83071000
Country of origin	DE

WP-STEEL PVC C 17 - Protective hose



3240869

<https://www.phoenixcontact.com/gb/products/3240869>

Technical data

Notes

Notes on operation	Protective hose length is measured stretched out; length tolerance $\pm 5\%$
--------------------	--

Product properties

Product type	Protective hose
Tensile strength GRP	500 N

Data management status

Article revision	00
------------------	----

Dimensions

Internal dimensions

Internal diameter	13 mm
-------------------	-------

Material specifications

Material	Steel, galvanized / PVC
----------	-------------------------

Cable/line

Bending radius, dynamic	115 mm
Bending radius, static	45 mm
Tensile strength	500 N
Halogen-free	no

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68
Ambient temperature (operation)	-25 °C ... 90 °C
Short-term temperature	100 °C

WP-STEEL PVC C 17 - Protective hose



3240869

<https://www.phoenixcontact.com/gb/products/3240869>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3240869>



VDE Zeichengenehmigung

WP-STEEL PVC C 17 - Protective hose



3240869

<https://www.phoenixcontact.com/gb/products/3240869>

Classifications

ECLASS

ECLASS-11.0	27430301
ECLASS-12.0	27430301
ECLASS-13.0	27430301

ETIM

ETIM 9.0	EC001179
----------	----------

UNSPSC

UNSPSC 21.0	40141700
-------------	----------

WP-STEEL PVC C 17 - Protective hose



3240869

<https://www.phoenixcontact.com/gb/products/3240869>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk