

## Stripping and cutting tools

### Stripping and cutting tools

- for flexible and solid conductors with PVC insulation
- Cable with double insulation in two processing steps without special adjustment
- Automatic opening of clamping jaws after stripping
- No play in self-adjusting cutting unit
- Long-lasting
- No splicing of single conductors
- Optimised ergonomic design
- Stripping length adjustable via stop
- Adjustable for different insulation thicknesses
- switchable partial stripping function
- Removable handle shells
- Fold-out cutting protection
- Custom marking with ESG device markers

### stripax®

0.08 - 10 mm<sup>2</sup>

n



### stripax® 16

6 - 16 mm<sup>2</sup>

n



- Stripping: PVC insulated flexible conductor, size 0.08...10 mm<sup>2</sup> (~AWG 28...7)
- Cutting: PVC insulated flexible conductor, size 0.08...6 mm<sup>2</sup> (~AWG 28...10)
- Conductors undamaged due to special self adjusting stripping blades.
- Processing of multi-conductors, with thin flat ribbon cables and even multiple conductors in one operation

- Stripping: PVC insulated flexible and solid conductors (~AWG 10...6)
- Cutting: PVC insulated flexible and solid conductors, up to 6 mm<sup>2</sup> (AWG 10)
- Conductors undamaged due to special self adjusting stripping blades.



### Technical data

Max. stripping performance	
Cable type	
Conductor cross-section	mm <sup>2</sup>
Stripping length, max.	mm
Cutting performance	
Max. cutting performance	mm <sup>2</sup>
Tool data	
Length	mm
Weight	g
Note	

stripax®		
Flexible and solid conductors with PVC insulation		
Conductor cross-section	mm <sup>2</sup>	0.08...10
Stripping length, max.	mm	25
Max. cutting performance	mm <sup>2</sup>	6
Length	mm	190
Weight	g	175
Note		

stripax® 16		
Flexible and solid conductors with PVC insulation		
Conductor cross-section	mm <sup>2</sup>	6...16
Stripping length, max.	mm	25
Max. cutting performance	mm <sup>2</sup>	6
Length	mm	190
Weight	g	175
Note		

### Ordering data

Version
Note

Type	Qty.	Order No.
stripax®	1	9005000000
Note		

Type	Qty.	Order No.
stripax® 16	1	9005610000
Note		

### Accessories

Type	Qty.	Order No.
Spare stripping blades	1	1119030000
Note		

Type	Qty.	Order No.
Spare stripping blades	1	1119030000
Note		

Type	Qty.	Order No.
Spare stripping blades	1	1119040000
Note		