

SHOWA 577 Gray

Foamed nitrile over fully dipped nitrile coating, over engineered fiber reinforced with HPPE

[FEATURES

- Multifilament polyester wrapping DURACoil liner reinforced with HPPE
- EN 388:2016 Cut Level C
- ANSI/ISEA 105-16: A3
- Fully coated nitrile, with an extra nitrile finish on palm for good grip & aeration
- Unique SHOWA ergonomic shape that replicates the natural curve of the human hand
- Seamless knit
- High abrasion resistance level 4

[BENEFITS

- Increased cut resistance performance due to engineered DURACoil wrapping technology
- Foamed nitrile coating with a film nitrile coating providing high abrasion resistance while remaining breathable
- Maximum comfort when performing delicate tasks due to soft and flexible HPPE properties combined with high multifilament wrapping technique
- High level of flexibility and dexterity due to advanced grip technology
- Liquid-proof to end of coated area
- Optimal grip performance in wet & oily conditions
- Ergonomically designed to replicates the natural curves for enhanced dexterity and longer use
- Cost-efficient gloves that can be laundered and re-used

[INDUSTRY



Aerospace



Automotive



Construction



Glass



Manufacturing



Mechanical



Oil and Gas

[IDEAL APPLICATIONS

- Mechanical and engineering
- Plumbing
- Canning
- Mounting and dismantling
- Handling heavy equipment



MATERIAL

- Engineered yarn
- HPPE
- Polyester

COATING

- Foam nitrile
- Nitrile

STANDARDS

ANSI / ISEA
105-2016



CUT

SHOWA

577

Gray



PACKAGING

- 12 Pair per polybag
- 6 Polybags per case
- 72 Pair per case



SIZES

- 6/S
- 7/M
- 8/L
- 9/XL
- 10/XXL



COLOUR

- Gray



[YOU MIGHT ALSO BE INTERESTED IN

SHOWA
546



MATERIAL
Engineered yarn
COATING
Polyurethane

SHOWA
477



MATERIAL
Acrylic
COATING
Nitrile

SHOWA
377



MATERIAL
Polyester
COATING
Foam nitrile

SHOWA
386



MATERIAL
Engineered yarn
COATING
Microporous nitrile

[USER INSTRUCTIONS

Do not use where there are chemical, electrical, thermal or entanglement risks. Wash at 40°C max. Performance levels as per standard EN388 retained after 3 washes, subject to variations linked to actual usage conditions. The performance levels apply to the coated surface only. Store in a dry place, away from the light.

[DISCLAIMER

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

Get in touch

SHOWA USA | 579 Edison Street - Menlo, GA 30731, USA

USA@SHOWAgroup.com

© SHOWA Group 2018 | All rights reserved