

---

## 64150

OSRAM ORIGINAL LINE | Halogen headlight lamps for cars



---

### Areas of application

- Headlight

---

### Product benefits

- OEM Quality
- Wide product range
- Reliable quality

---

### Product features

- Original spare parts

# Product datasheet

## Technical data

### Electrical data


Power input	68 W <sup>1)</sup>
Nominal wattage	55.00 W
Nominal voltage	12 V
Test voltage	13.2 V

<sup>1)</sup> Maximum

### Photometrical data

Color temperature	3200 K
Luminous flux	1550 lm
Luminous flux tolerance	±15 %

### Dimensions & weight



Length	67.5 mm
Diameter	9.0 mm
Product weight	6.89 g

### Lifespan

Lifespan B3	400 h
Lifespan Tc	650 h

### Additional product data

Base (standard designation)	P14.5s
-----------------------------	--------

### Certificates & standards

ECE category	H1
--------------	----

### Country specific categorizations

## Product datasheet

<b>Order reference</b>	64150 55W 12V P
------------------------	-----------------

---

### Country specific information

<b>Product code</b>	<b>METEL code</b>	<b>SEG number</b>	<b>STK number</b>	<b>UK Org</b>
4050300001487	OSRA64150	8328000	4739951	-
4050300925264	OSRA64150BL1	8328378	4730314	-

## Product datasheet

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4050300001487	64150	Folding carton box 1	25 mm x 23 mm x 70 mm	0.04 dm <sup>3</sup>	8.10 g
4050300206820	64150	Bundle 10	90 mm x 68 mm x 79 mm	0.48 dm <sup>3</sup>	82.00 g
4050300206837	64150	Shipping carton box 100	122 mm x 109 mm x 361 mm	4.80 dm <sup>3</sup>	915.00 g
4050300880181	64150	Unpacked 1	22 mm x 15 mm x 36 mm	0.01 dm <sup>3</sup>	5.00 g
4050300311258	64150	Shipping carton box 320	255 mm x 240 mm x 345 mm	21.11 dm <sup>3</sup>	3304.40 g
4050300925264	64150	Blister 1	79 mm x 28 mm x 105 mm	0.23 dm <sup>3</sup>	16.71 g
4008321142009	64150	Shipping carton box 10	107 mm x 145 mm x 225 mm	3.49 dm <sup>3</sup>	242.33 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.