

MERKMALE

- Gusseisen-Schraubstock-Konstruktion
- Stahlbacken
- Um 360° drehbarer Schraubstockkopf
- G-Klemmenbefestigung

Tischschraubstock von RS Pro x 30 mm, 65 mm x 60 mm

RS Best.-Nr. 752-2428



Professionelle Produkte von RS bieten Ihnen hochwertige Teile in allen Produktkategorien. Unsere Produktpalette wurde von Ingenieuren getestet und bietet eine vergleichbare Qualität wie die führenden Marken, ohne einen Premium-Preis zu zahlen.

Produktbeschreibung

Dieser leichte Tischschraubstock von RS Pro ist ideal für allgemeine Anwendungen und wird auf einer drehbaren Plattform für 360°-Einstellung montiert. Dieser Schraubstock besteht aus hochwertigem Gusseisen und verfügt über eine einstellbare G-Klemme zur Befestigung auf Oberflächen. Diese einfache Klemmwirkung bedeutet, dass der Schraubstock sehr mobil und vielseitig ist. Der feste Sockel und die starken Greifbacken sorgen für volles Vertrauen in professionelle Anwendungen.

Allgemeine

Schraubstock	G-Klemm-Schraubstock
Anwendungen	Holzarbeiter und Zimmerleute, Ingenieure und Metallarbeiter, Mechaniker, Hobbyisten und Enthusiasten

Mechanische

Backenöffnung	60mm
Backenbreite	65mm
Backentiefe	30mm
Backenhöhe	30mm
Drehbarer Schraubkopf	360°
Montage	Klammer
Gewicht	2.1Kg



Order Code	Manufacturers Code	Description
752-2428	52-192-875	G-Clamp Vice

Maximum Jaw Opening	60mm
Jaw Width	65mm
Jaw Height	30mm
Maximum Table Clamping	40mm
Rotating Vice Head	360°
Flat Anvil Size	30 x 40mm
Vice Head Material	Cast Iron
Table Clamp Material	Cast Iron
Vice Guide Rods	Steel
Vice Jaw Material	Steel
Weight	2.1K

1	Vice Jaws
2	Vice Handle
3	Swivelling Vice Head
4	Table / Bench Clamp Bracket
5	Clamp Screw
6	Swivel Lock
7	Flat Anvil



This lightweight portable mini vice is suitable for use in engineering, automotive and home workshops and can be easily mounted to any convenient working surface

Maximum Jaw Opening	60mm
Jaw Width	65mm
Jaw Height	30mm
Maximum Table Clamping	40mm
Rotating Vice Head	360°



Maximum Jaw Opening	60mm
Jaw Width	65mm
Jaw Height	30mm
Maximum Table Clamping	40mm
Rotating Vice Head	360°
Flat Anvil Size	30 x 40mm
Vice Head Material	Cast Iron
Table Clamp Material	Cast Iron
Vice Guide Rods	Steel
Vice Jaw Material	Steel
Weight	2.1K

1	Vice Jaws
2	Vice Handle
3	Swivelling Vice Head
4	Table / Bench Clamp Bracket
5	Clamp Screw
6	Swivel Lock
7	Flat Anvil