

ANTISTATIC 2200 ELECTRONIC-SERVICE-SET

The tool set for mobile use at electrostatically endangered components



2200

2200 **BERNSTEIN** SERVICE-SET **ANTISTATIC** with tool set

2201 Case with zip fastener, without tools

2220 **BERNSTEIN** SERVICE-SET **ANTISTATIC**
with tool set in **conductive** case

2221 Conductive case with zip fastener, without tools

Description:

Elegant, black zipper case, with wine red lining and transparent pockets for 12 tools and a foldable antistatic workbench pad with accessories. Art. 2220 complete made from conductive black imitation leather.

Outside dimensions: 320 x 250 x 50 mm (when closed)



2220

Weight with tools: approx. 0.950 kg

Tool set:

| No. | Description of individual tools |
|----------|--|
| 2-620 | PLCC extractor |
| 3-601-13 | Side cutters , 120 mm, for hard wire up to 0.4 mm Ø , for soft wire up to 1.0 mm Ø , bright steel-polished, box joint, double leaf spring, with conductive black hand-guard |
| 3-632-13 | Flat nose pliers , 120 mm, bright steel-polished, box joint, double leaf spring, with conductive black hand-guard |
| 3-633-13 | Snipe nose pliers , 120 mm, bright steel-polished, box joint, double leaf spring, with conductive black hand-guard |
| 4-601 | Screwdriver 50 x 0.8 mm , with conductive handle, blade from chrome vanadium, chrome-plated, with black tip |
| 4-605 | Screwdriver 60 x 2.0 mm , with conductive handle, blade from chrome vanadium, chrome-plated, with black tip |
| 4-606 | Screwdriver 60 x 2.5 mm , with conductive handle, blade from chrome vanadium, chrome-plated, with black tip |
| 4-621 | Cross-recess screwdriver size 000 , with conductive handle, blade from chrome vanadium, chrome-plated, with black tip |

| No. | Description of individual tools |
|-------|--|
| 4-622 | Cross-recess screwdriver size 00 , with conductive handle, blade from chrome vanadium, chrome-plated, with black tip |
| 4-623 | Cross-recess screwdriver size 0 , with conductive handle, blade from chrome vanadium, chrome-plated, with black tip |
| 5-191 | Tweezers , 120 mm, made from conductive plastic material, reinforced with glassfibre, with straight, rounded tips |
| 5-192 | Tweezers , 120 mm, made from conductive plastic material, reinforced with glassfibre, with straight, 3 mm flat-hand tips |
| 9-354 | ESD handling set , consisting of: foldable, green workbench pad (surface resistance according to DIN 53482: approx. 10 ⁸ ohm), 500 x 400 x 0.35 mm, contact bracelet 9-342, earth wire 2500 mm long with 1 Mohm safety resistor |