


Features

- IEC-584-3
- Fast response, welded exposed junction
- Miniature Plug termination

RS PRO PTFE insulated Twin Twisted IEC Exposed Junction Thermocouple with Miniature Plug - Type K

RS Stock No.: 0652778



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Fast response welded exposed junction available in Class 1 cable specification with a Miniature plug termination.

Ideal for test and development applications.

General Specifications

Thermocouple Type	Type K
Temperature Measurement Range	-75°C to +260°C
Construction	Terminated with a miniature flat pin plug
Measuring Junction	Exposed
Standards Met	IEC
Application	Fast response, welded exposed junction

Mechanical Specifications

Termination	Miniature Plug
Length	0.3m (0.98ft)
Cable Insulation	1/0.2mm Teflon® PTFE insulated twin-twisted lead

Approvals

Declarations	RoHS
--------------	------

Similar Products

Colour Code	Type	Style	Cable Size	Length	Termination	RS Stock#
IEC	J	PTFE	1/0.2mm	0.3m (0.98ft)	Miniature Plug	0652754
IEC	J	PTFE	1/0.2mm	1m (3.3ft)	Miniature Plug	3630244
IEC	J	PTFE	1/0.2mm	1m (3.3ft)	Miniature Plug	2623205 (x10)
IEC	J	PTFE	1/0.2mm	2m (6.56ft)	Miniature Plug	1236308
IEC	J	PTFE	1/0.2mm	3m (9.84ft)	Miniature Plug	2209486
IEC	J	PTFE	1/0.2mm	5m (16.4 ft)	Miniature Plug	1236309
IEC	J	PTFE	1/0.2mm	10m (32.8ft)	Miniature Plug	1236310
IEC	K	PTFE	1/0.2mm	0.3m (0.98ft)	Miniature Plug	0652778
IEC	K	PTFE	1/0.2mm	1m (3.3ft)	Miniature Plug	3630250
IEC	K	PTFE	1/0.2mm	1m (3.3ft)	Miniature Plug	2623206 (x10)
IEC	K	PTFE	1/0.2mm	2m (6.56ft)	Miniature Plug	1104482
IEC	K	PTFE	1/0.2mm	2m (6.56ft)	Miniature Plug	2623191 (x10)
IEC	K	PTFE	1/0.2mm	3m (9.84ft)	Miniature Plug	2209487
IEC	K	PTFE	1/0.2mm	5m (16.4 ft)	Miniature Plug	1236306
IEC	K	PTFE	1/0.2mm	5m (16.4 ft)	Miniature Plug	2623192 (x10)
IEC	K	PTFE	1/0.2mm	10m (32.8ft)	Miniature Plug	1236307
IEC	K	PTFE	1/0.2mm	10m (32.8ft)	Miniature Plug	2623193 (x5)
IEC	T	PTFE	1/0.2mm	0.3m (0.98ft)	Miniature Plug	0652779
IEC	T	PTFE	1/0.2mm	1m (3.3ft)	Miniature Plug	3630266
IEC	T	PTFE	1/0.2mm	1m (3.3ft)	Miniature Plug	2623207 (x10)
IEC	T	PTFE	1/0.2mm	2m (6.56ft)	Miniature Plug	1236311
IEC	T	PTFE	1/0.2mm	2m (6.56ft)	Miniature Plug	2623195 (x5)
IEC	T	PTFE	1/0.2mm	3m (9.84ft)	Miniature Plug	2209488
IEC	T	PTFE	1/0.2mm	5m (16.4 ft)	Miniature Plug	1236312
IEC	T	PTFE	1/0.2mm	5m (16.4 ft)	Miniature Plug	2623196 (x10)
IEC	T	PTFE	1/0.2mm	10m (32.8ft)	Miniature Plug	1236313