

AWC-01

Full HD 1080p Autofocus Webcam
with Microphone



Full HD
1080p resolution



Autofocus



Built-in
Microphone



Detachable
Privacy lens cover

We're live, right now!

Setup your workspace professionally, whether you are at home or in the office, with the versatile Verbatim AWC-01 webcam. Keep your video calls crystal clear with Full 1080p HD resolution and 2K at 30fps.

The autofocus function ensures that your face remains clear on camera while the auto white balance adjusts the video for well-exposed lifelike colours, even in dim lighting.

With a 75° field of view, the camera captures head and shoulders plus some of your background, giving a glimpse into your workspace.

AWC-01

Full HD 1080p Autofocus Webcam with Microphone

PN	Description	Bar Code	EAN128 Code	EAN14 Code
49578	Verbatim AWC-01 Full HD 1080P Autofocus Webcam with Microphone	023942495789	(02)00023942495789(37)10(91)482 (02)00023942495789(37)40(91)482	20023942495783 50023942495784

General Information

Material	ABS Plastic	Colour	Black
Product Dimensions LxWxH (mm)	80 x 76 x 32	Product Weight (grams) approx	102
Plug'n'Play	Yes	Mounting options	monitor, desktop, tripod*

Connection

USB Interface	USB 2.0 Type-A	Cable Length	1.5m (detachable)
---------------	----------------	--------------	-------------------

Camera

Sensor	1/4" CMOS	Lens	8 MP
Resolution	2K	Max Frame Rate	30 fps
Definition	1080P FHD HD/QHD supported	FPS	2560x1440@ 30fps 1920x1080@ 30fps
Focus	Automatic	Automatic white balance	Yes
Autofocus distance	15cm-∞	Face Tracking	No
Viewing Angle (diagonally)	75°	Privacy Shutter	Yes (detachable)

Microphone

Built-in Microphone	Yes	Polar Pattern	Omnidirectional
Sensitivity	-26±1dB (0dB=1V/Pa, at 1KHz)	Noise reduction	No
		Frequency	1 kHz

Other Features

Tripod Interface	Yes, 1/4" thread	Rotatable	No
Anti-slip mat	Yes	Snapshot button	No
LED Indicators	No	LED Light	No

Storage and Operating Conditions

Storage Temperature	~-10°C to ~60°C
Operating Temperature	0° to ~60° C
Operating Humidity	25% to 60% RH (non-condensing)

Logistic Information

Pack Dimensions LxWxH (mm)	146 x 80 x 60
Pack Weight (grams) approx	156.7
Units per Pack	1
Inner Carton Dimensions LxWxH (mm)	325 x 175 x 165
Pcs per Inner Carton	10
Outer Cartons Dimensions LxWxH (mm)	370 x 345 x 345
Pcs per Outer Carton	40
Outer Carton per Layer	9
Layers per Pallet	5
Pcs per Pallet	1 800

Privacy lens cover open



Privacy lens cover closed



System Requirements:

- Interface USB 2.0 (also compatible with USB 3.2 Gen 1 ports)
- Windows 11, 10, 8, 7
- Mac OS X 10.6 or above
- Linux kernel 2.6 or above
- Android Chrome 29.0.1547 or above

Supported video-conference SW :

Zoom, Teams, OBS, Facebook, Youtube, Xbox one, XSplit, Skype, Twitch, Google Meet

Pack Contents:

- Verbatim AWC-01 Full HD 1080p Autofocus Webcam with Microphone
- USB 2.0 Micro-USB to USB-A cable
- Detachable privacy lens cover
- Quick Start Guide

Warranty

- 2 Year Limited Warranty

* Tripod is not included

For more information, please contact your key account manager

www.verbatim.com

AWC-01

Full HD 1080p Autofocus Webcam with Microphone

Image library

Download high-res images from the marketing directory:
www.verbatim-marcom.com



Product front - Closed clip



Mounted - Privacy Mode



Left Angled view - Open clip



Left Angled view - Additional Info



Angled on tripod



Packaging 3D



Lifestyle 1



Lifestyle 2



Lifestyle 3



Lifestyle 4