







UNDERVOLTAGE RELEASE 380-400 V AC 50/60 HZ ACCESSORY FOR 3VA1 and 3VA20 up to 3VA25

Model					
product brand name	SENTRON				
product designation	Accessories				
design of the product	auxiliary release				
accessories	Auxiliary release				
General technical data					
degree of pollution	3				
overvoltage category	III				
apparent power consumption / maximum	2.5 VA				
Voltage					
surge voltage resistance	4 kV				
Mechanical Design					
height	65.1 mm				
width	25.7 mm				
number of slots	3				
depth	28.8 mm				
net weight	91 g				
tightening torque / with screw-type terminals / minimum	0.4 N·m				
tightening torque / with screw-type terminals / maximum	0.5 N·m				
Connections according IEC					
stripped length	10 mm				
AWG number / as coded connectable conductor cross section / for auxiliary contacts					
• minimum	20				
• maximum	16				
Connections according UL					
stripped length [in]	0.4 in				
tightening torque [lbf·in] / with screw-type terminals / minimum	3.5 lbf·in				
tightening torque [lbf·in] / with screw-type terminals / maximum	4.4 lbf·in				
Certificates					
General Product Approval	EMC	Declaration of Conformity	Test Certificates		
Miscellaneous					Miscellaneous
Test Certificates	Marine / Shipping	other	Environment		

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9908-0BB26>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9908-0BB26>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9908-0BB26


CAx-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





last modified:

8/15/2023 

