


# Product Data Sheet

## MaxiDry® Zero™ 56-451

<b>Colour – Coating</b>	Purple/black
<b>Colour – Liner</b>	Dark blue
<b>Design</b>	Fully coated knitwrist
<b>Coating</b>	NBR (Nitrile Butadiene Rubber)
<b>Coating texture</b>	Micro-Foam with Non-Slip Grip
<b>Liner</b>	Nylon, Acrylic
<b>Patent number</b>	EP 1 608 808
<b>Palm thickness</b>	2.00 mm



### Dimensions

Size Range	Size 7 (S)	Size 8 (M)	Size 9 (L)	Size 10 (XL)	Size 11 (XXL)
Total glove length (+/-10 mm)	250	260	270	280	290
Wrist length (mm)	98	98	100	100	102
Wrist width (mm)	96	96	100	104	104
Palm width (+/-3 mm)	110	115	118	125	130
Over lock colour	Red	Orange	White	Yellow	Black

### EN test Results

Test	Notified Body	Result/Pass
EN ISO 21420: 2020	TÜV Rheinland	Yes
EN 388: 2016 + A1: 2018	TÜV Rheinland	4232B
EN 407: 2004	TÜV Rheinland	X1XXXX
EN 511: 2006	TÜV Rheinland	021



# Product Data Sheet

## MaxiDry® Zero™ 56-451

### Typical Performance Values

EN 388:2016 + A1:2018 A. Abrasion Resistance	> 8000 Cycles
EN 388:2016 + A1:2018 B. Cut Resistance	> 2.5 index
EN 388:2016 + A1:2018 C. Tear Resistance	> 50 newtons
EN 388:2016 + A1:2018 D. Puncture Resistance	> 60 newtons
EN 388:2016 + A1:2018 E. Cut Resistance ISO	≥ 5 Newton

### HandCare®

Skin Health Alliance Dermatologically Accredited	Yes
REACH compliant	Yes
Standard 100 by OEKO-TEX® (08.BH.57867)	Certified
Washable	40°
Sanitized®	Yes



### Special features

Silicone free	-
Liquid proof	Yes
Food contact	Yes (FDA, EC 1935/2004)



# Product Data Sheet

## MaxiDry® Zero™ 56-451

### Packaging

<b>Pairs per poly bag</b>	6
<b>Poly bags per carton</b>	12
<b>Carton count</b>	72
<b>Carton dimensions (mm)</b>	500 x 295 x 270

### Weight

<b>Size Range</b>	<b>Size 7 (S)</b>	<b>Size 8 (M)</b>	<b>Size 9 (L)</b>	<b>Size 10 (XL)</b>	<b>Size 11 (XXL)</b>
Glove weight / Pair (+/-6 gram)	110	116	128	132	144
Gross Weight (Kg)	9	9.5	10.3	10.65	11.5
Carton Weight (Kg)	1	1	1	1	1
Net Weight (Kg)	8	8.5	9.3	9.6	10.5

Issue date: 24.06.2019

