

8790 B Impaktor Deep Socket with 3/8" drive, 22 x 63 mm

Sockets 3/8"



| | | | |
|------------------------|----------------------|-------------------------------|--------------|
| EAN: | 4013288233202 | Size: | 130x45x32 mm |
| Part number: | 05005562001 | Weight: | 204 g |
| Article number: | 8790 B Impaktor Deep | Country of origin: | TW |
| | | Customs tariff number: | 82042000 |

- Robust Impaktor sockets for extremely high stress; for use with electric or pneumatic wrenches with 3/8" drive
- Long sockets for low lying couplings, also suitable for fitting, protruding thread rods in confined spaces
- Hexagon profile for precise and profile-friendly screwdriving at high power transmission
- With Take it easy tool finder: colour coding by size
- With cross hole and ring socket to attach the safety pin and safety ring of machine operated tools

Long Impaktor socket for use with electric or pneumatic wrenches with 3/8" drive. Also usable at low-lying couplings and protruding thread rods. The Impaktor technology ensures higher-than-average service life even at extreme requirements. With Take it easy tool finder with colour coding by size - for quick and easy identification of the required tool. With hexagon profile and socket with hole. The hexagon profile offers the transmission of high forces and loads the edges of the bolt or the screw head less than a double hexagon profile. For external hexagon bolts and screws.

Web link

<https://www.wera.de/en/05005562001>

Wera - 8790 B Impaktor Deep
05005562001 - 4013288233202

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Sockets 3/8"

For electric or pneumatic wrenches



The extremely robust forged design ensures higher-than-average service life of the Impaktor sockets even at extreme requirements.

Long design




Thanks to the long design of the sockets, even couplings in tight spaces can be reached. Screwdriving at protruding thread rods can also be possible.

Cross hole and ring socket



Thanks to the hole and the ring socket, the tools can be held securely on the power tool with a safety pin or an O-ring.

Profile-friendly power transmission



The hexagon profile offers the transmission of high forces and loads the edges of the bolt or the screw head less than a double hexagon profile. Fine-toothed ratchets also make use of a double hexagon profile superfluous, even in confined spaces, thanks to their small return angle.

Take it easy tool finder system



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklus bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklus sockets and Zyklus bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklus bit sockets).

Web link






<https://www.wera.de/en/05005562001>

Wera - 8790 B Impaktor Deep
05005562001 - 4013288233202

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Sockets 3/8"

Further versions in this product family:

| | |  |  |  |  |  |
|--------------------|--------------------------------|---|---|--|---|---|
| | | mm | inch | mm | mm | mm |
| 05005550001 | leuchtpink_232C | 8.0 | - | 63.0 | 14.1 | 19.0 |
| 05005551001 | leuchtgelb_yellowC | 10.0 | - | 63.0 | 16.6 | 19.0 |
| 05005552001 | cyan_2985C | 11.0 | - | 63.0 | 17.8 | 20.0 |
| 05005553001 | schwarz_blackC | 12.0 | - | 63.0 | 18.2 | 20.0 |
| 05005554001 | tuerkis_339C | 13.0 | - | 63.0 | 20.0 | 22.0 |
| 05005555001 | pink_241C | 14.0 | - | 63.0 | 21.0 | 22.0 |
| 05005556001 | weiss | 15.0 | - | 63.0 | 22.0 | 22.0 |
| 05005557001 | violett_2735C | 16.0 | - | 63.0 | 25.0 | 22.0 |
| 05005558001 | rot_200C | 17.0 | - | 63.0 | 26.0 | 23.0 |
| 05005559001 | leuchtgruen_375C | 18.0 | - | 63.0 | 28.0 | 23.0 |
| 05005560001 | blau_307C | 19.0 | - | 63.0 | 27.0 | 25.0 |
| 05005561001 | gruen_363C | 21.0 | - | 63.0 | 30.0 | 27.0 |
| 05005562001 | leuchtgelb_yellow C | 22.0 | - | 63.0 | 32.0 | 28.0 |
| 05005563001 | cyan_2985C | 24.0 | - | 63.0 | 34.0 | 30.0 |
| 05005564001 | leuchtgelb_yellowC | - | 1/4" | 63.0 | 11.0 | 19.0 |
| 05005565001 | blau_307C | - | 5/16" | 63.0 | 14.1 | 19.0 |
| 05005566001 | rot_200C | - | 3/8" | 63.0 | 16.6 | 19.0 |
| 05005567001 | violett_2735C | - | 7/16" | 63.0 | 17.8 | 19.0 |
| 05005568001 | tuerkis_339C | - | 1/2" | 63.0 | 20.0 | 22.0 |
| 05005569001 | pink_241C | - | 9/16" | 63.0 | 21.0 | 22.0 |
| 05005570001 | schwarz_blackC | - | 5/8" | 63.0 | 24.0 | 22.0 |
| 05005571001 | cyan_2985C | - | 11/16" | 63.0 | 25.0 | 23.0 |
| 05005572001 | gelb_123C | - | 3/4" | 63.0 | 28.0 | 25.0 |
| 05005573001 | blau_307C | - | 13/16" | 63.0 | 30.0 | 27.0 |
| 05005574001 | leuchtgruen_375C | - | 7/8" | 63.0 | 32.0 | 28.0 |
| 05005575001 | rot_200C | - | 15/16" | 63.0 | 34.0 | 30.0 |
| 05005576001 | tuerkis_339C | - | 1" | 63.0 | 36.0 | 32.0 |

Web link

<https://www.wera.de/en/05005562001>

 Wera - 8790 B Impaktor Deep
 05005562001 - 4013288233202

 Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de