

Wiha XSelector and XLSelector.

Couldn't be smaller!

Wiha XLSelector.

Couldn't be smaller: for 25 mm bits.



The range of Wiha bit selectors is distinguished by incredible compactness and ingeniously simple bit removal.

With the new 31-piece XLSelector and the 11-piece XSelector, Wiha offers an optimum range that has been tailored to user requirements.

The proven colour-coding system facilitates identification of the various bit qualities.



The XLSelector is extremely flat and compact and fits in every case.



The Wiha XSelector: bit removal couldn't be easier.

Protector with System Loop: for attaching the 11-piece XSelector to a belt or for wall-mounting.



Wiha XLSelector.

- Extremely flat and compact bit box, stocked with 30 bits and bit holder
- Bit box with soft zones for a non-slip grip and comfortable handling
- Removal of the bits couldn't be easier
- With dimensions of just 135 x 80 x 17.5 mm, it even fits into a shirt or trouser pocket
- Due to its compactness, it's ideal for storing in a toolbox



Wiha XSelector.

- Compact, smart, tidy!
- Equipped with 10 bits and bit holder
- Ingeniously simple bit removal via integrated bit clamp
- With dimensions of just 75 x 53 x 15 mm, it fits in every shirt or trouser pocket
- Together with the Protector, can be attached to a belt

ZOT Torsion and Security bits.



7948-047 XLSelector Torsion, mixed, 31 pcs.
Housing: Box made of high quality plastic. The simplest bit removal guaranteed.
Bits: 25 mm ZOT Torsion and Standard bits.
Geometry: Patented torsion zone to prevent premature breaking of the bit when under stress.
Holder: ClicFix quick release holder, magnetic.
Application: Especially suitable for fastenings in metal and hard materials – it can't get any more compact!
Extra: Soft zones for maximum working comfort.

Order-No.	Series	
29415 1	7948-047	5
①	7010 ZOT	1x5.5 1x6.5 1x8.0
⊕	7011 ZOT	2xPH1 5xPH2 2xPH3
⊕	7012 ZOT	2xPZ1 5xPZ2 2xPZ3
⊙	7013 Z	1x4.0 1x5.0 1x6.0
⊙	7015 ZOT	1xT10 1xT15 1xT20 1xT25 1xT30 1xT40
7149	ClicFix quick release holder, magnetic, style E 6.3	



7948-927 XLSelector Standard, Security, 31 pcs.
Housing: Box made of high quality plastic. The simplest bit removal guaranteed.
Bits: 25 mm ZOT Torsion and Standard bits.
Holder: ClicFix quick release holder, magnetic.
Application: All types of fastenings for trade and industry – it can't get any more compact!
Extra: Soft zones for maximum working comfort. Bits for popular security screws.

Order-No.	Series	
29416 8	7948-927	5
⊕	7019 ZOT TW	1x0 1x1 1x2 1x3 1x4
⊕	7019 Z SP	1x4 1x6 1x8 1x10
⊙	7013 Z TR	1xTR2.0 1xTR2.5 1xTR3.0 1xTR4.0 1xTR5.0 1xTR6.0
⊕	7019 ZOT TS	1x6 1x8 1x10
⊕	7015 Z TR	1xT8H 1xT9H 1xT10H 1xT15H 1xT20H
⊙	7018 Z	1xT25H 1xT27H 1xT30H 1xT40H 1x1 1x2 1x3
7149	ClicFix quick release holder, magnetic, style E 6.3	

HOT Torsion and Standard bits.



7948-005 XLSelector Standard, mixed, 31 pcs.
Housing: Box made of high quality plastic. The simplest bit removal guaranteed.
Bits: 25 mm Standard bits.
Holder: Universal holder, magnetic.
Application: All types of fastenings for trade and industry – it can't get any more compact!
Extra: Soft zones for maximum working comfort.

Order-No.	Series	
29417 5	7948-005	5
①	7010 Z	1x4.5 1x5.5 1x6.5
⊕	7011 Z	2xPH1 4xPH2 1xPH3
⊕	7012 Z	2xPZ1 5xPZ2 1xPZ3
⊙	7015 Z	2xT10 2xT15 2xT20 3xT25 2xT30 1xT40
7113 S	Universal holder, magnetic, style E 6.3	



7948-255 XLSelector Torsion/ Standard, mixed, 31 pcs.
Housing: Box made of high quality plastic. The simplest bit removal guaranteed.
Bits: 25 mm HOT Torsion and Standard bits.
Geometry: Patented torsion zone to prevent premature breaking of the bit when under stress.
Holder: Universal holder, magnetic.
Application: Especially suitable for fastenings in wood and soft materials – it can't get any more compact!
Extra: Soft zones for maximum working comfort. Extra hard Wiha HOT Torsion bits for optimum wear properties with soft screw applications, ideal for turning screws in wood.

Order-No.	Series	
29418 2	7948-255	5
⊕	7012 HOT	3xPZ1 10xPZ2 2xPZ3
⊙	7015 Z	2xT10 2xT15 3xT20 4xT25 2xT30 2xT40
7113 S	Universal holder, magnetic, style E 6.3	

Wiha XLSelector.

Couldn't be smaller: for 25 and 50 mm bits.

Inkra and Standard bits.



7948-92801 **XLSelector, Standard, mixed, 21 pcs.**
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 50 mm Inkra bits and 25 mm Standard bits.
Holder: CentroFix quick release holder, magnetic, style E 6.3.
Application: All types of fastenings for trade and industry – it can't get any more compact!
Extra: Soft zones for maximum working comfort.

Order-No.	Series							
33664 6	7948-92801							5
⊕	7011 Z	1xPH1	1xPH2	1xPH3				
⊕	7012 Z	1xPZ1	1xPZ2	1xPZ3				
⊕	7015 Z	1xT10	1xT15	2xT20	1xT25	1xT30	1xT40	
⊕	7041 Inkra	1xPH1	1xPH2	1xPH3				
⊕	7042 Inkra	1xPZ1	1xPZ2	1xPZ3				
Ⓢ	7010 Z	1x6.5						
	7148C	CentroFix quick release holder, style E 6.3						





7948-0502 **XLSelector, Standard, TORX®, 21 pcs.**
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 25 mm and 50 mm Standard bits.
Holder: CentroFix quick release holder, magnetic, style E 6.3.
Application: All types of fastenings for trade and industry – it can't get any more compact!
Extra: Soft zones for maximum working comfort The TORX® ball end enables fastening and unfastening at an angle of up to 25°.

Order-No.	Series							
32803 0	7948-0502							5
⊕	7045BE	1xT10	1xT15	1xT20	1xT25	1xT30	1xT40	
⊕	7015TT	1xT15	1xT20	1xT25	1xT30			
⊕	7015 Z TR	1xT15H	2xT20H	2xT25H	1xT30H			
⊕	7016 Z	1x15IP	1x20IP	1x25IP	1x30IP			
	7148C	CentroFix quick release holder, style E 6.3						

ZOT Torsion and Standard bits.



7948-0501 **XLSelector, Standard, TORX® ball end, 13 pcs.**
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 50 mm TORX® ball end Standard bits.
Holder: CentroFix quick release holder, magnetic, style E 6.3.
Application: All types of fastenings for trade and industry – it can't get any more compact!
Extra: Soft zones for maximum working comfort.
The TORX® ball end enables fastening and unfastening at an angle of up to 25°.

Order-No.	Series						
32802 3	7948-0501						5
	7045BE	1xT9	1xT10	2xT15	2xT20		
		2xT25	1xT27	2xT30	1xT40		
	7148C	CentroFix quick release holder, style E 6.3					



7948-928 **XLSelector, Torsion, mixed, 13 pcs.**
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 50 mm ZOT Torsion bits.
Holder: CentroFix quick release holder, magnetic, style E 6.3.
Application: Especially suitable for fastenings in metal and hard materials – it can't get any more compact!
Extra: Soft zones for maximum working comfort.

Order-No.	Series							
33663 9	7948-928							5
⊕	7041 ZOT	1xPH1	1xPH2	1xPH3				
⊕	7042 ZOT	1xPZ1	1xPZ2	1xPZ3				
⊕	7045 Z	1xT10	1xT15	1xT20	1xT25	1xT30	1xT40	
	7148C	CentroFix quick release holder, style E 6.3						

Wiha XSelector.

Couldn't be smaller!

DuraBits with torsion zone.






7944-0DR7 **XSelector Dura, mixed, 11 pcs.**
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 25 mm DuraBits with torsion zone.
Extremely wear-resistant Dura tip with hard-metal coating grips into the screw head and prevents the bit from slipping.
Geometry: Patented torsion zone to prevent premature breaking of the bit when under stress.
Coating: Hard-metal coating, extremely wear-resistant.
Holder: ClicFix quick release holder, magnetic.
Application: Bits for fatigue-free, safe work in demanding industrial applications and for sensitive surfaces – it can't get any more compact!

Order-No.	Series				
26974 6	7944-0DR7				10
Ⓢ	7010 DR	1x5.5	1x6.5		
⊕	7011 DR	1xPH1	2xPH2	1xPH3	
⊕	7012 DR	1xPZ1	2xPZ2	1xPZ3	
	7149	ClicFix quick release holder, magnetic, style E 6.3			



7944-9DR7 **XSelector Dura, mixed, 11 pcs.**
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 25 mm DuraBits with torsion zone.
Extremely wear-resistant Dura tip with hard-metal coating grips into the screw head and prevents the bit from slipping.
Geometry: Patented torsion zone to prevent premature breaking of the bit when under stress.
Coating: Hard-metal coating, extremely wear-resistant.
Holder: ClicFix quick release holder, magnetic.
Application: Bits for fatigue-free, safe work in demanding industrial applications and for sensitive surfaces – it can't get any more compact!

Order-No.	Series						
26975 3	7944-9DR7						10
	7012 DR	1xPZ1	2xPZ2	2xPZ3			
	7015 DR	1xT15	1xT20	1xT25	1xT30	1xT40	
	7149	ClicFix quick release holder, magnetic, style E 6.3					

SB7944-9DR7 **XSelector Dura, mixed, 11 pcs.**
Blister packed for hanging.

Order-No.	Series				
27001 8	SB7944-9DR7				10

Diamond bits and TiN Torsion bits.



7944-0D7 **XSelector Diamond, mixed, 11 pcs.**
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 25 mm Diamond Torsion bits.
Geometry: Patented torsion zone to prevent premature breaking of the bit when under stress.
Coating: Extremely wear-resistant diamond-sapphire coating with a long service life.
Holder: ClicFix quick release holder, magnetic.
Application: Bits for fatigue-free work; bits ideal for frequent fastening – it can't get any more compact!

Order-No.	Series				
26976 0	7944-0D7				10
Ⓢ	7010 D	1x5.5	1x6.5		
⊕	7011 D	1xPH1	2xPH2	1xPH3	
⊕	7012 D	1xPZ1	2xPZ2	1xPZ3	
	7149	ClicFix quick release holder, magnetic, style E 6.3			



7944-065 **XSelector TiN, mixed, 11 pcs.**
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 25 mm TiN Torsion bits.
Geometry: Patented torsion zone to prevent premature breaking of the bit when under stress.
Coating: TiN coating, extends the tool life.
Holder: Universal holder, magnetic.
Application: Bits for trade and industry, especially with series connections – it can't get any more compact!

Order-No.	Series				
26977 7	7944-065				10
Ⓢ	7010 TiN	1x5.5	1x6.5		
⊕	7011 TiN	1xPH1	2xPH2	1xPH3	
⊕	7012 TiN	1xPZ1	2xPZ2	1xPZ3	
	7113 S	Universal holder, magnetic, style E 6.3			

SB7944-065 **XSelector TiN, mixed, 11 pcs.**
Blister packed for hanging.

Order-No.	Series				
27003 2	SB7944-065				10

Wiha XSelector.

Couldn't be smaller!

ZOT Torsion bits.



7944-045 XSelector Torsion, mixed, 11 pcs.
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 25 mm ZOT Torsion bits.
Geometry: Patented torsion zone to prevent premature breaking of the bit when under stress.
Holder: Universal holder, magnetic.
Application: Especially suitable for fastenings in metal and hard materials – it can't get any more compact!

Order-No.	Series				
26978 4	7944-045				10
①	7010 ZOT	1x5.5	1x6.5		
⊕	7011 ZOT	1xPH1	2xPH2	1xPH3	
⊗	7012 ZOT	1xPZ1	2xPZ2	1xPZ3	
	7113 S	Universal holder, magnetic, style E 6.3			

SB7944-045 XSelector Torsion, mixed, 11 pcs.
Blister packed for hanging.

Order-No.	Series				
27004 9	SB7944-045				10



7944-145 XSelector Torsion, Phillips, 11 pcs.
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 25 mm ZOT Torsion bits.
Geometry: Patented torsion zone to prevent premature breaking of the bit when under stress.
Holder: Universal holder, magnetic.
Application: Especially suitable for fastenings in metal and hard materials – it can't get any more compact!

Order-No.	Series				
26979 1	7944-145				10
⊕	7011 ZOT	2xPH1	6xPH2	2xPH3	
	7113 S	Universal holder, magnetic, style E 6.3			

ZOT Torsion bits and HOT Torsion bits.



7944-245 XSelector Torsion, Pozidriv, 11 pcs.
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 25 mm ZOT Torsion bits.
Geometry: Patented torsion zone to prevent premature breaking of the bit when under stress.
Holder: Universal holder, magnetic.
Application: Especially suitable for fastenings in metal and hard materials – it can't get any more compact!

Order-No.	Series				
26980 7	7944-245				10
⊕	7012 ZOT	2xPZ1	6xPZ2	2xPZ3	
	7113 S	Universal holder, magnetic, style E 6.3			

SB7944-245 XSelector Torsion, Pozidriv, 11 pcs.
Blister packed for hanging.

Order-No.	Series				
27006 3	SB7944-245				10



7944-055 XSelector Torsion, mixed, 11 pcs.
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 25 mm HOT Torsion bits.
Geometry: Patented torsion zone to prevent premature breaking of the bit when under stress.
Holder: Universal holder, magnetic.
Application: Especially suitable for fastenings in wood and soft materials – it can't get any more compact!

Order-No.	Series				
29412 0	7944-055				10
①	7010 HOT	1x5.5	1x6.5		
⊕	7011 HOT	1xPH1	2xPH2	1xPH3	
⊗	7012 HOT	1xPZ1	2xPZ2	1xPZ3	
	7113 S	Universal holder, magnetic, style E 6.3			

Standard bits.



7944-005 XSelector Standard, mixed, 11 pcs.
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 25 mm Standard bits.
Holder: Universal holder, magnetic.
Application: All types of fastenings for trade and industry – it can't get any more compact!



Order-No.	Series				
26982 1	7944-005				10
①	7010 Z	1x5.5	1x6.5		
⊕	7011 Z	1xPH1	2xPH2	1xPH3	
⊗	7012 Z	1xPZ1	2xPZ2	1xPZ3	
	7113 S	Universal holder, magnetic, style E 6.3			

SB7944-005 XSelector Standard, mixed, 11 pcs.
Blister packed for hanging.

Order-No.	Series				
27008 7	SB7944-005				10



7944-505 XSelector Standard, TORX®, 11 pcs.
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 25 mm Standard bits.
Holder: Universal holder, magnetic.
Application: All types of fastenings for trade and industry – it can't get any more compact!

Order-No.	Series						
26983 8	7944-505						10
	7015 Z	1xT7	1xT8	1xT9	1xT10	1xT15	
		1xT20	1xT25	1xT27	1xT30	1xT40	
	7113 S	Universal holder, magnetic, style E 6.3					



SB7944-505 XSelector Standard, TORX®, 11 pcs.
Blister packed for hanging.

Order-No.	Series				
27009 4	SB7944-505				10

Standard bits.



7944-505TR XSelector Standard, TORX® H, 11 pcs.
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 25 mm Standard bits.
Suitable for TORX® Tamper Resistant security screws.
Holder: Universal holder, magnetic.
Application: All types of fastenings for trade and industry – it can't get any more compact!

Order-No.	Series						
26984 5	7944-505TR						10
	7015 Z TR	1xT7H	1xT8H	1xT9H	1xT10H	1xT15H	
		1xT20H	1xT25H	1xT27H	1xT30H	1xT40H	
	7113 S	Universal holder, magnetic, style E 6.3					

SB7944-505TR XSelector Standard, TORX® H, 11 pcs.
Blister packed for hanging.

Order-No.	Series				
27010 0	SB7944-505TR				10



7944-904 XSelector Standard, mixed, 11 pcs.
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 25 mm Standard bits.
Holder: Universal holder, magnetic.
Application: All types of fastenings for trade and industry – it can't get any more compact!

Order-No.	Series				
26985 2	7944-904				10
⊕	7011 Z	1xPH1	1xPH2	1xPH3	
⊗	7012 Z	1xPZ1	1xPZ2	1xPZ3	
⊗	7015 Z	1xT15	1xT20	1xT25	1xT30
	7113 S	Universal holder, magnetic, style E 6.3			

SB7944-904 XSelector Standard, mixed, 11 pcs.
Blister packed for hanging.

Order-No.	Series				
27011 7	SB7944-904				10

Wiha XSelector.

Couldn't be smaller!

Standard bits.



7944-905 XSelector Standard, mixed, 11 pcs.
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 25 mm Standard bits.
Holder: Universal holder, magnetic.
Application: All types of fastenings for trade and industry – it can't get any more compact!

Order-No.	Series					
26986 9	7944-905					10
⊕	7012 Z	1xPZ1	2xPZ2	2xPZ3		
⊗	7015 Z	1xT15	1xT20	1xT25		
		1xT30	1xT40			
	7113 S	Universal holder, magnetic, style E 6.3				

SB7944-905 XSelector Standard, mixed, 11 pcs.
Blister packed for hanging.

Order-No.	Series					
27012 4	SB7944-905					10



7944-906 XSelector Standard, mixed, 11 pcs.
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 25 mm Standard bits.
Holder: Universal holder, magnetic.
Application: All types of fastenings for trade and industry – it can't get any more compact!

Order-No.	Series					
26987 6	7944-906					10
⊕	7011 Z	1xPH1	2xPH2	2xPH3		
⊗	7015 Z	1xT15	1xT20	1xT25		
		1xT30	1xT40			
	7113 S	Universal holder, magnetic, style E 6.3				

SB7944-906 XSelector Standard, mixed, 11 pcs.
Blister packed for hanging.

Order-No.	Series					
27013 1	SB7944-906					10

Standard bits.



7944-902 XSelector Standard, hex, 9 pcs.
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 25 mm Standard bits.
Holder: Universal holder, magnetic.
Application: All types of fastenings for trade and industry – it can't get any more compact!
Extra: With hex bits up to size 8 mm.

Order-No.	Series					
27157 2	7944-902					10
⦿	7013 Z	1x1.5	1x2.0	1x2.5	1x3.0	
		1x4.0	1x5.0	1x6.0	1x8.0	
	7113 S	Universal holder, magnetic, style E 6.3				



7944-995 XSelector Standard, SIT, 11 pcs.
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 25 mm SIT bits.
Holder: Universal holder, magnetic.
Application: All types of fastenings for trade and industry – it can't get any more compact!
Extra: With bits to fit ASSY® and Plas screws.

Order-No.	Series					
27321 7	7944-995					10
⦿	7019 Z SIT	2xSIT 10	3xSIT 20	2xSIT 25		
		2xSIT 30	1xSIT 40			
	7113 S	Universal holder, magnetic, style E 6.3				

Wiha XSelector and XLSelector.

Couldn't be smaller!

Inkra bits.



7944-015 XSelector Inkra, mixed, 11 pcs.
Housing: Box made of high quality plastic.
The simplest bit removal guaranteed.
Bits: 25 mm Inkra bits.
Holder: Turning screws is easy, even if screwdriver is at an angle.
Universal holder, magnetic.
Application: The ideal bits for all hard-to-reach places, especially suitable for wood screws – it can't get any more compact!

Order-No.	Series					
26988 3	7944-015					10
⊕	7011 Inkra	1xPH1	3xPH2	1xPH3		
⊗	7012 Inkra	1xPZ1	3xPZ2	1xPZ3		
	7113 S	Universal holder, magnetic, style E 6.3				

SB7944-015 XSelector Inkra, mixed, 11 pcs.
Blister packed for hanging.

Order-No.	Series					
27014 8	SB7944-015					10



7944 Protector with System-Loop.
Customised holder for the XSelector.
Material: High quality, impact resistant plastic.
Application: For wall mounting or as a belt attachment when combined with the System Loop.

Order-No.	Series					
27026 1						10

TEST WINNING BITS

Stiftung Warentest

test

+

GUT (1,6)

Im Test: 17 Bit-Sets mit unterschiedlichen Bit-Sorten Phillips / Pozidriv

Ausgabe 2/2007

Sales counter display XSelector and XLSelector.



7948 VB1 XLSelector Standard, display.
6 XLSelectors 7948-005.

Order-No.						
29541 7	6 XLSelectors 7948-005					
①	7010 Z	1x4.5	1x5.5	1x6.5		
⊕	7011 Z	2xPH1	4xPH2	1xPH3		
⊗	7012 Z	2xPZ1	5xPZ2	1xPZ3		
⦿	7015 Z	2xT10	2xT15	2xT20	3xT25	2xT30 1xT40
	7113 S	Universal holder, magnetic, style E 6.3				



7944 VB5 XSelector Standard, display.
12 XSelectors 7944-005.

Order-No.						
27048 3	12 XSelectors 7944-005					
①	7010 Z	1x5.5	1x6.5			
⊕	7011 Z	1xPH1	2xPH2	1xPH3		
⊗	7012 Z	1xPZ1	2xPZ2	1xPZ3		
	7113 S	Universal holder, magnetic, style E 6.3				