

## Han Fast-Lock 4-6qmm ang.silverplat.+pin




Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 08 000 7223                                                                |
| Specification      | Han Fast-Lock 4-6qmm ang.silverplat.+pin                                      |
| HARTING eCatalogue | <a href="https://harting.com/09080007223">https://harting.com/09080007223</a> |

### Identification

|                            |                            |
|----------------------------|----------------------------|
| Category                   | Contacts                   |
| Series                     | Han-Fast <sup>®</sup> Lock |
| Type of contact            | PCB contact                |
| Description of the contact | With pin<br>Angled         |

### Version

|               |                |
|---------------|----------------|
| Pack contents | Single contact |
|---------------|----------------|

### Technical characteristics

|                         |                         |
|-------------------------|-------------------------|
| Conductor cross-section | 4 ... 6 mm <sup>2</sup> |
| Rated current           | ≤60 A                   |
| Contact resistance      | ≤2 mΩ                   |
| Stripping length        | 7.5 mm                  |

### Material properties

|                     |                                                        |
|---------------------|--------------------------------------------------------|
| Material (contacts) | Copper alloy                                           |
| Surface (contacts)  | Silver plated                                          |
| Material (locking)  | Copper alloy                                           |
| Surface (locking)   | Passivated                                             |
| RoHS                | compliant with exemption                               |
| RoHS exemptions     | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status          | compliant with exemption                               |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| China RoHS                           | 50                                   |
| REACH Annex XVII substances          | Not contained                        |
| REACH ANNEX XIV substances           | Not contained                        |
| REACH SVHC substances                | Yes                                  |
| REACH SVHC substances                | Lead                                 |
| ECHA SCIP number                     | b51e5b97-eeb5-438b-8538-f1771d43c17d |
| California Proposition 65 substances | Yes                                  |
| California Proposition 65 substances | Lead                                 |
|                                      | Nickel                               |

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 100                                      |
| Net weight                     | 2.367 g                                  |
| Country of origin              | Germany                                  |
| European customs tariff number | 85366990                                 |
| GTIN                           | 5713140188624                            |
| eCl@ss                         | 27460201 PCB connector (board connector) |
| ETIM                           | EC002637                                 |
| UNSPSC 24.0                    | 39121415                                 |