

EBT-CA 750 Bluetooth



The EvoTorque® Battery Tool - Compact Advanced (EBT-CA) is engineered for professionals who demand precision and reliability. Delivering up to 20% more portability without sacrificing performance, this compact tool features intelligent joint sensing technology for exact torque application every time. Its patented cooling system ensures extended operation under heavy use, while the lightweight, ergonomic design offers superior manoeuvrability in tight spaces. Ideal for industries where safety and accuracy are critical. Fully compatible with our latest software, [ToolSync](#) and [TorqApp](#)™, which are designed to seamlessly capture torque tightening data via Bluetooth®.

Part number: 181475

EAN Bar Code: 5060922236739

NATO number: -

Accuracy: Up to $\pm 3\%$

Operates between:

75.00 - 750.00 N·m



TECHNICAL SPECIFICATIONS

- Tool Weight: 3.1 kg
- Square Drive: 3/4"
- Reaction Plate Weight: 0.8 kg
- Output Speed (rpm): 12.5 rpm
- Battery Weight: 0.8 kg

FEATURES

- The EBT-CA torque multiplier utilises PC software accessible through the Norbar website, a mobile application is also available to download from dedicated app sites
- The PC software and app can be used to retrieve results, view tool diagnostics, configure Presets, User IDs and Job Presets
- Advanced Torque modes include: Torque, Torque then Angle, Angle Only, Torque with Angle and Audit Mode
- Intelligent joint sensing technology ensures precise torque application, preventing over-torque and increasing accuracy
- Best-in-class Norbar-designed gearbox ensures reliability and durability in the toughest environments
- Ergonomic and lightweight design improves operator comfort and makes it easier to handle in confined spaces
- Up to 20% more compact design for enhanced portability and ease of use
- Clear top-mounted display provides real-time torque data and allows for quick and easy adjustments to settings
- 'Safe to Start' feature minimises the risk of accidental activation, increasing safety in the workplace
- Powered by an 18V, 5.0 Ah battery, providing excellent fastener performance and extended battery life per charge
- Supplied with 2 batteries, 1 single-bay battery charger, cranked reaction, operator's manual, and a convenient carry case
- Supplied with torque and angle calibration certificate
- Typical storage capacity: 4,000 readings (Results Only mode) or 1,500 readings (Results + Graph mode)

Norbar Torque Tools India Pvt. Ltd. Plot No A-168, Khairne Industrial Area, Thane
Belapur Road, Mahape, Navi Mumbai - 400 709. INDIA

- Tel: + 91 22 2778 8480 / 2030
- Email: enquiry@norbar.in