

XL SPLINE RATCHETING WRENCHES




Surface Drive Plus™ reduces fastener rounding and delivers up to 25% more torque

Ratcheting box-end needs as little as 5° to move a fastener vs. 30° for standard box end wrenches

Up to 25% longer to access those hard to reach fasteners


Spline Ratcheting Wrenches work on a wide assortment of fasteners including E-Torx, Square, 6-Point 50% rounded, 12-Point, 6-Point, and Spline



Spline Ratcheting Wrenches work on a wide assortment of fasteners.

| GearWrench Part # | Spline | 6 Pt. | 6 Pt. (50% rounded) | 12 Pt. | Square | E-Torx® |
|-------------------|--------|--------|---------------------|--------|--------|---------|
| 85548 | #8 | 1/4" | 1/4" | 1/4" | - | E-8 |
| 85550 | #10 | 5/16" | 5/16" | 5/16" | 1/4" | E-10 |
| 85552 | #12 | 3/8" | 3/8" | 3/8" | 5/16" | E-12 |
| 85554 | #14 | 7/16" | 7/16" | 7/16" | 3/8" | E-14 |
| 85556 | #16 | 1/2" | 1/2" | 1/2" | - | E-16 |
| 85558 | #18 | 9/16" | 9/16" | 9/16" | 7/16" | E-18 |
| 85560 | #20 | 5/8" | 5/8" | 5/8" | 1/2" | E-20 |
| 85562 | #22 | 11/16" | 11/16" | 11/16" | 9/16" | E-22 |
| 85564 | #24 | 3/4" | 3/4" | 3/4" | 5/8" | E-24 |

Titanium Silver Gear





85598 - 9 Pc. XL Spline Combination Ratcheting Wrench Set SAE

| Item No. | Description |
|----------|--|
| 85548 | #8 x 1/4" XL Spline Ratcheting Wrench |
| 85550 | #10 x 5/16" XL Spline Ratcheting Wrench |
| 85552 | #12 x 3/8" XL Spline Ratcheting Wrench |
| 85554 | #14 x 7/16" XL Spline Ratcheting Wrench |
| 85556 | #16 x 1/2" XL Spline Ratcheting Wrench |
| 85558 | #18 x 9/16" XL Spline Ratcheting Wrench |
| 85560 | #20 x 5/8" XL Spline Ratcheting Wrench |
| 85562 | #22 x 11/16" XL Spline Ratcheting Wrench |
| 85564 | #24 x 3/4" XL Spline Ratcheting Wrench |



Open Stock - XL Spline Combination Ratcheting Wrenches

| Item # | Opening Inches | A | B | C | D | E | Weight (lbs) |
|--------|----------------|--------|-------|-------|-------|-------|--------------|
| 85548 | #8 x 1/4" | 5.315 | 0.610 | 0.256 | 0.571 | 0.181 | 0.121 |
| 85550 | #10 x 5/16" | 5.906 | 0.650 | 0.256 | 0.709 | 0.197 | 0.196 |
| 85552 | #12 x 3/8" | 7.087 | 0.778 | 0.287 | 0.906 | 0.224 | 0.227 |
| 85554 | #14 x 7/16" | 7.677 | 0.854 | 0.303 | 0.984 | 0.248 | 0.296 |
| 85556 | #16 x 1/2" | 8.661 | 0.984 | 0.339 | 1.102 | 0.276 | 0.347 |
| 85558 | #18 x 9/16" | 9.252 | 1.035 | 0.370 | 1.260 | 0.295 | 0.385 |
| 85560 | #20 x 5/8" | 10.236 | 1.201 | 0.406 | 1.378 | 0.315 | 0.517 |
| 85562 | #22 x 11/16" | 10.827 | 1.240 | 0.421 | 1.496 | 0.354 | 0.577 |
| 85564 | #24 x 3/4" | 12.008 | 1.339 | 0.441 | 1.654 | 0.374 | 0.771 |


85204 - 3 Pc. QuadBox™ Double Box Ratcheting Wrench Set SAE

| Item No. | Description |
|----------|--|
| 85201 | QuadBox Ratcheting Wrench 5/16", 3/8", 7/16", 1/2" |
| 85202 | QuadBox Ratcheting Wrench 9/16", 5/8", 11/16", 3/4" |
| 85203 | QuadBox Ratcheting Wrench 13/16", 7/8", 15/16", 1" |



85215 - 4 Pc. QuadBox™ Double Box Ratcheting Wrench Set METRIC

| Item No. | Description |
|----------|---|
| 85211 | QuadBox Ratcheting Wrench 8 mm, 10 mm, 12 mm, 13 mm |
| 85212 | QuadBox Ratcheting Wrench 16 mm, 17 mm, 18 mm, 19 mm |
| 85213 | QuadBox Ratcheting Wrench 9 mm, 11 mm, 14 mm, 15 mm |
| 85214 | QuadBox Ratcheting Wrench 20 mm, 21 mm, 22 mm, 24 mm |



Open Stock - QuadBox™ Ratcheting Wrenches SAE/METRIC

| Item # | Opening Inches | A | B | C | D | E | Weight (lbs) |
|--------|---------------------------|--------|-------|-------|-------|-------|--------------|
| 85201 | 5/16", 3/8", 7/16", 1/2" | 6.299 | 0.780 | 0.472 | 0.969 | 0.591 | 0.185 |
| 85202 | 9/16", 5/8", 11/16", 3/4" | 8.268 | 1.181 | 0.669 | 1.343 | 0.748 | 0.449 |
| 85203 | 13/16", 7/8", 15/16", 1" | 11.417 | 1.535 | 0.906 | 1.791 | 1.102 | 1.10 |
| 85211 | 8, 10, 12, 13 mm | 6.299 | 0.780 | 0.472 | 0.969 | 0.591 | 0.189 |
| 85212 | 16, 17, 18, 19 mm | 9.055 | 1.252 | 0.709 | 1.339 | 0.787 | 0.491 |
| 85213 | 9, 11, 14, 15 mm | 7.087 | 0.854 | 0.512 | 1.130 | 0.630 | 0.253 |
| 85214 | 20, 21, 22, 24 mm | 11.417 | 1.535 | 0.866 | 1.791 | 1.024 | 1.056 |