

AF73 - Araflame Work Lightweight FR

Coverall

Collection: Araflame™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Araflame Work: 93% Meta Aramid, 5% Para Aramid, 2% Carbon Fibre, 150g

Outer Carton: 18



Product information

This super lightweight coverall offers outstanding flame resistant protection. The Araflame fabric is soft and breathable but provides excellent tear and tensile strength. Ideal for a variety of industries including oil and gas, petrochemical and many more. The coverall's features include triple stitching throughout, secure pockets and waist elastication for ease of movement.

Araflame™ Work

Araflame™ Work has been developed for comfort and performance. Certified to several international standards, these garments offer outstanding protection at all times. The high quality fabric combined with the ergonomic fit provide all day comfort and style.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, F1)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 3.8 CAL/CM², ATPV 4.5 CAL/CM²)

EN 17353 Type B2

ASTM F1959/F1959M-12 (ATPV 5.9 CAL/CM² (HAF 63.1%))

Features

- Inherent flame resistant qualities will not diminish with washing
- Protection against radiant, convective and contact heat
- Two back patch pockets
- Triple-stitched seams for extra durability
- Durable, strong and long lasting brass zips
- Hook and loop cuffs for a secure fit
- Sew on flame resistant industrial wash tape
- Radio loops for easy clipping of a radio
- Sleeve pocket
- Two-way front durable brass zip for easy access
- 8 pockets for ample storage

AF73 - Araflame Work Lightweight FR Coverall
Commodity Code: 6211331000

Test House

Aitex (Notified Body No.: NB: 0161)
 Plaza Emilio Sala 1
 , ESPAGNE
 Cert No: 19/1623/01/0161

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
AF73ORR32	Orange	43.0	28.0	50.0	0.7300	0.0602	5036108331352	25036108819649
AF73ORR34	Orange	43.0	28.0	50.0	0.7400	0.0602	5036108327874	25036108816679
AF73ORR36	Orange	43.0	28.0	50.0	0.7340	0.0602	5036108279982	25036108770018
AF73ORR38	Orange	43.0	28.0	50.0	0.7820	0.0602	5036108279999	25036108770025
AF73ORR40	Orange	43.0	28.0	50.0	0.8020	0.0602	5036108280001	25036108770032
AF73ORR42	Orange	43.0	28.0	50.0	0.7880	0.0602	5036108280018	25036108770049
AF73ORR44	Orange	43.0	28.0	50.0	0.8120	0.0602	5036108280025	25036108770056
AF73ORR46	Orange	43.0	28.0	50.0	0.8360	0.0602	5036108280032	25036108770063
AF73ORR48	Orange	43.0	28.0	50.0	0.8600	0.0602	5036108280049	25036108770070
AF73ORR50	Orange	43.0	28.0	50.0	0.8200	0.0602	5036108280056	25036108770087
AF73ORR52	Orange	43.0	28.0	50.0	0.8380	0.0602	5036108280063	25036108770094
AF73ORR54	Orange	43.0	28.0	50.0	0.8610	0.0602	5036108280070	25036108770100