

## DUSTING TOOLS V-2200

### V-2200

#### Dual Extender Set for AIR DUSTER



EAN: 9 00330862200 5

#### DUSTING TOOLS

extend our range of GREEN-CLEAN aerosols AIR + VACUUM POWER into multifunctional tools. Extremely robust and designed for repeated use on many cans. The improved method is time-saving due to better working advantages, at the same time preventing the use of unnecessary one way part.

#### Anwendungsvorteile DUAL EXTENDER – Verlängerungen zu TOP VENTIL

- Adapter for optional use with plastic extension tube or pipe with stable metal tip
- 360° action radius even in confined components
- No loss of liquid gas in any position - even when can is full. (So-called upside down versions require 2/3 empty space in the can)
- Use of pipe increases the action radius to 70 cm; that of the capillary tube to 25 cm



To use with GREEN CLEAN AIR POWER:

G-2016	150 ml / 173 gr	not flammable
G-2041	400 ml / 342 gr	flammable
G-2051	400 ml / 462 gr	not flammable



#### Technical Details:

Beschreibung	Maße in cm	Gewicht	Private Logo	Material:
TOP VENTIL V-2000 + metal adapter for flexible pipe or fixed capillary tube	Pipe 50 cm	67,3 gr.		Top Valve: POM + Aluminium Adapter: PP Tube: PVC
Packaging	Units			
Box	4 Units	21,0 x 8,0 x 20,5	373,7 gr.	<b>Shipping</b>
Box	12 Units	27,0 x 21,5 x 20,7	1,00 kg	No reg.
Pallet / Rows	15 x 12 Units = 180 Units	15,03 kg	<b>Tariff Number</b>	<b>Chem. Reg.</b>
max. Rows :	6 Rows = 1080 Units	90,18 kg	8428995	No reg.

## DUSTING TOOLS V-2200

### V-2200

### Dual Extender Set zu AIR DUSTER



EAN: 9 00330862200 5

**DUSTING TOOLS** erweitern GREEN CLEAN AirDuster zum multifunktionalen Werkzeug zum Ausblasen oder Absaugen, mit Anti Static Wirkung oder mit Verlängerungen

### Anwendungsvorteile DUAL EXTENDER – Verlängerungen zu TOP VENTIL

- Adapter zur wahlweisen Verwendung
- mit starrem Kapillarrohr oder
- flexiblem Schlauch mit stabiler Metallspitze
- 360° Aktionsradius auch in engen Bauteilen
- in keiner Position flüssiger Gasaustritt auch bei hohem Dosenfüllstand
- Schlauchanwendung erweitert den Aktionsradius auf 60 cm, mit Kapillarrohr auf 25 cm
- Dose um 0,36 EUR billiger als Einwegversion



Zu verwenden mit GREEN CLEAN AIR POWER:

G-2016	150 ml / 173 gr	unbrennbar
G-2041	400 ml / 342 gr	brennbar
G-2051	400 ml / 462 gr	unbrennbar



### Technische Beschreibung:

Beschreibung	Maße in cm	Gewicht	Private Logo	Material:
TOP VENTIL V-2000 + Metalladapter für flexiblen Schlauch oder starrem Kapillarrohr	Schlauch 50 cm	67,3 gr.		Top Ventil: POM + Alu Adapter: PP Schlauch PVC
<b>Verpackung</b>	<b>Stück</b>			
Kreuzhülle	4 Stk.	21,0 x 8,0 x 20,5	373,7 gr.	<b>Versand</b>
Karton	12 Stk.	27,0 x 21,5 x 20,7	1,00 kg	keine Vo
PaLETTE je Reihe	15 x 12 Stk = 180 Stk.	15,03 kg	<b>ZollPosnr.</b>	<b>ChemVo</b>
max. Reihen :	6 Reihen = 1080 Stk.	90,18 kg	8428995	keine Vo
				<b>Lagerung</b>
				keine Vo