

















# PRODUCT SPECIFICATION

<b>Brand</b>	C.K
<b>Product Range</b>	Switch key
<b>Catalogue number</b>	4454
<b>Date</b>	09/05/2012

<b>Range Description</b> Universal Switch Key 6In1				
<b>Features</b> <ul style="list-style-type: none"> <li>A multipurpose tool designed for use on locking systems of: gas, electric, and water cupboards in industry and/or technical equipment in buildings such as air conditioning, stop valves, mains consoles, doors etc.</li> </ul>				
<b>Item Number</b>	<b>Item Description</b>	<b>EAN No</b>	<b>Commodity code</b>	<b>Carton Qty</b>
T4454	Universal switch key 6in1	5013969981599	82041100	1

<p>Technical product information</p>	<p>Body – Die cast Aluminium  Double ended screwdriver bit: PH1 x slotted 1.0x7mm</p> <p>Adaptors:</p> <table border="0"> <tr> <td data-bbox="480 421 724 495"> <p>Outside diameter 13mm  Square A/F 7-8mm</p> </td> <td data-bbox="914 421 991 495">  </td> </tr> <tr> <td data-bbox="480 528 724 602"> <p>Outside diameter 12mm  Square A/F 6mm</p> </td> <td data-bbox="914 528 991 602">  </td> </tr> <tr> <td data-bbox="480 636 724 710"> <p>Outside diameter 9mm  Square A/F 5mm</p> </td> <td data-bbox="914 636 991 710">  </td> </tr> <tr> <td data-bbox="480 743 724 817"> <p>Outside diameter 13mm  Triangle A/F 8-9mm</p> </td> <td data-bbox="914 743 991 817">  </td> </tr> <tr> <td data-bbox="480 851 724 925"> <p>Across lugs 14mm  Bore 3-5mm</p> </td> <td data-bbox="914 851 991 925">  </td> </tr> </table> <p>A/F = Across Flats</p> <p>Also includes 6mm hex holder for Screwdriver bit</p>	<p>Outside diameter 13mm  Square A/F 7-8mm</p>		<p>Outside diameter 12mm  Square A/F 6mm</p>		<p>Outside diameter 9mm  Square A/F 5mm</p>		<p>Outside diameter 13mm  Triangle A/F 8-9mm</p>		<p>Across lugs 14mm  Bore 3-5mm</p>	
<p>Outside diameter 13mm  Square A/F 7-8mm</p>											
<p>Outside diameter 12mm  Square A/F 6mm</p>											
<p>Outside diameter 9mm  Square A/F 5mm</p>											
<p>Outside diameter 13mm  Triangle A/F 8-9mm</p>											
<p>Across lugs 14mm  Bore 3-5mm</p>											
<p>Standards compliance</p>	<p>None applicable</p>										
<p>User health and safety information</p>	<p>None applicable</p>										
<p>RoHS/WEEE compliance</p>	<p>This product range does not fall within the scope of RoHS or WEEE regulations</p>										
<p>Material safety data</p>	<p>None applicable</p>										
<p>Warranty</p>	<p>C.K switch keys are guaranteed for life against imperfect materials or workmanship</p>										
<p>Country of origin</p>	<p>Germany</p>										

## Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T4454	40	25	73	69	85	28	163	84

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T4454	-	-	-	-	-	-

## Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T4454	14	Blister	1	Insert	-	-	-	-