

TECHNICAL SPECIFICATION

EYE AND FACE PROTECTION



EVOGuard®C1 Industrial Visor

EVOGuard®C1 Industrial Visor / ADA240-060-000



DESCRIPTION

EVOGuard®C high performance industrial visors provide comprehensive facial coverage without limiting movement. The optical class 1 visor range offers UV protection and a panoramic view with minimal distortion.

Fully compatible with EVOGuard® browguard systems and EVO® helmet range, the C1 visor offers up to AT rated impact protection and is also suitable for use with the Force®8 half mask and P3 filters.

OPTIONS

EVOGuard®C1 Industrial Visor (ADA240-060-000)

SAFETY STANDARDS

EN 166 • EN 170



JSP Limited, Worsham Mill, Minster Lovell, Oxford OX29 0TA, England.

Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: sales@jsp-safety.com / Web: www.jsp-safety.com

Do Not Publish without written permission from JSP Limited. Contact copyright@jsp-safety.com. Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.

Page 1 of 2 / Issued 4 Feb 2022 / Copyright 2018 - 2022. JSP Limited. All Rights Reserved.



SPECIFICATIONS



RADIATION PROTECTION BREAKDOWN filtering effect
Scale Number
2C



LIGHT TRANSMISSION BREAKDOWN Lens Shade number
1.2



Manufacturer's Trademark
JSP Dagger



High Energy Impact resists a 6 mm, 0.86g ball @ 190 m/s
Maximum protection for face shields
A when fitted to an EVO® Helmet



Optical Class (1 – Class 1 – High quality for regular use. 2 – Class 2 – Medium quality for occasional use. 3 – Class 3 – Low quality for exceptional use)
1



The letter T, immediately after the mechanical strength symbol, authorises use for high speed particles at extreme temperatures. (-5°C and +55°C) Optional
T



Medium Energy Impact resists a 6 mm, 0.86g ball @ 120 m/s Maximum protection for goggles.
B When Fitted to EVOGuard® Browguard



Protection from Liquid Splash
3



Visor Length
18.5cm



BSI Kitemark
Yes



Product Weight
185g



Recyclable
Yes



Kit
Supplied With: EVO® 2,3,5,DS,Lite,Skyworker™ Arms. EVO8/EVOLite Badgeholder Arms. EVOGuard® Browguard Mounting System

FEATURES



Helmet & Browguard Integration

Fully compatible with *EVO® helmet and the EVOGuard® Browguard system*. Not including EVO®Vista® or EVO®6100 ranges



Compatibility

EVOGuard® visors maximise compatibility with JSP half masks, disposable respirators, prescription glasses and the Sonis® helmet mounted ear defender range.



Vision

The optical class 1 visor offers a panoramic view with minimal distortion, ideal for comfortable all day wear.



Impact

Five high performance visors offering up to A rated impact resistance when fitted to a safety helmet and fully compatible with EVOGuard® browguard for medium energy impact protection.



Coverage

EVOGuard® visors provide comprehensive facial coverage without limiting movement. EVOGuard® MAX visors offer enhanced coverage with an integral chinguard.



UV Protection

Visor filters harmful UV radiation to protect the eyes whilst also offering high light transmission and enhanced colour recognition.

RANGE

VIDEOS



www.youtube.com/watch?v=_VnTgBRRT9E

DOWNLOADS



[Image Pack \(ZIP\)](#)



[Declaration of Conformity \(PDF\)](#)



JSP Limited, Worsham Mill, Minster Lovell, Oxford OX29 0TA, England.

Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: sales@jspsafety.com / Web: www.jspsafety.com

Do Not Publish without written permission from JSP Limited. Contact copyright@jspsafety.com. Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.

Page 2 of 2 / Issued 4 Feb 2022 / Copyright 2018 - 2022. JSP Limited. All Rights Reserved.

