

FEATURES

- General purpose crocodile clip.
- Manufactured from bright mild steel.
- Large (30mm) jaw opening makes it suitable as a battery clip.
- The integral cable clamp has a secure 4mm screw fixing.
- The enhanced finger grip ensures a simple operation

RS PRO Banana Plugs & Connectors – Crocodile Clip, 25A

RS Stock No.: 2121207



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Banana Plugs & Connectors



Product Description

Crocodile Clip - Large

General purpose crocodile clip.

Manufactured from bright mild steel.

Large (30mm) jaw opening makes it suitable as a battery clip.

The integral cable clamp has a secure 4mm screw fixing.

The enhanced finger grip ensures a simple operation

General Specifications

Clip Material	Bright Mild Steel CS4, nickel plated	
Screw / Nut & Washer Material	M4 x 6mm, Steel, Nickel plated	

Electrical Specifications

Voltage Rating	50V
Current Rating	25A

Operation Environment Specifications

Operating Temperature	-20 TO +60°C	
-----------------------	--------------	--

Approvals

Declarations	RoHS Certificate of Compliance
--------------	--------------------------------

Banana Plugs & Connectors




Similar Products

Parameters	1037249	1806619	1806620
Brand	RS PRO	RS PRO	RS PRO
Туре	Crocodile Clip - Standard	Crocodile Clip - Miniature Black	Crocodile Clip - Miniature Red
Current Rating	5A	8A	8A
Jaw Opening	15 mm	8mm	8mm
Contact Material	Nickel Plated Steel	Nickel Plated Brass	Nickel Plated Brass
Insulated	No	Yes	Yes
Colour	Nickel	Black	Red
Insulation Material	N/A	Polypropylene	Polypropylene

Parameters	1806619	1806620	1806615	1806616
Brand	RS PRO	RS PRO	RS PRO	RS PRO
Туре	Insulating Cover for Large Crocodile Clip 1806618 - Black	Insulating Cover for Large Crocodile Clip 1806618 - Red	Insulating Cover for Standard Crocodile Clip 1037249 - Black	Insulating Cover for Standard Crocodile Clip 1037249 - Red
Colour	Black	Red	Black	Red
Insulation Material	PVC	PVC	PVC	PVC

Banana Plugs & Connectors





PVC INSULATED BOOT AVAILABLE IN RED 310-0500 OR BLACK 310-0100 OPERATING TEMPERATURE WITH BOOT FITTED -20 TO +60°C