

joystick controller - Ø 30 - 3 positions stay put - without contact Local distributor code:

387263939 9001K73

EAN Code: 3389118042711

Main

Range of product	Harmony 9001K
Product or component type	Head for joystick controller
Device short name	9001K
Sale per indivisible quantity	1
Type of operator	stay put
Operator profile	80 mm long operating shaft

Complementary

Bezel material	Metal
Mounting diameter	30 mm
Net weight	0.372 kg
Operating position	Any position
Shape of signaling unit head	Octagonal
Contacts type and composition	Without contact block
Device presentation	Basic element
Operator direction information	2 directions
Type of operator	Stay put
Size	30 mm

Environment

TC		
-4070 °C		
-2570 °C		
II conforming to IEC 61140		
IP66 conforming to IEC 60529		
NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 3R NEMA 4		

Standards	JIS C8201-5-1 IEC 60947-5-1		
	UL 508		
	IEC 60947-1		
	CSA C22.2 No 14		
	JIS C 852		
	IEC 60947-5-4		
	JIS C8201-1		
Product certifications	NEMA		
	UL 508		
Vibration resistance	tion resistance 7 gn (f= 2500 Hz) conforming to IEC 60068-2-6		
Shock resistance	50 gn conforming to IEC 60068-2-27		

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.1 cm
Package 1 Width	5.1 cm
Package 1 Length	13.3 cm
Package 1 Weight	240.0 g

Logistical informations

Country of origin

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d
REACh Regulation	REACh Declaration

Use Again


○ Repack and remanufacture	
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

9001K73

Mounting and Clearance

Contact Block Mounting Position


Top and Rear views



- (1) It is possible to mount up to 3 levels of contacts blocks (maximum of 6 contacts blocks)
- (2) Operator
- (3) Locating notch
- (4) Side 1
- (5) Side 2

Panel Cut-Out


Clearance




Legend plate	a min.		b min.	
	mm	in.	mm	in.
9001KN2••	57.2	2.25	44.5	1.75
9001KN3••	57.2	2.25	50.8	2.00

Individual Cut-outs Details

2 alternatives





Product datasheet

9001K73

Technical Description

Joystick Positions



Offer Marketing Illustration

Product benefits / Features



Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony 9001K

