


Features

- IEC-584-3
- Fast response, welded exposed junction
- Miniature Plug termination
- Unique single shot cable construction
Resistant to chemicals, oils and fluids. Suitable for aerospace applications and is widely used in autoclaves.

RS PRO PTFE Single Shot IEC Exposed Junction Thermocouple with Miniature Plug - Type K

RS Stock No.: 0652763



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Unique single shot cable construction Resistant to chemicals, oils and fluids. Suitable for aerospace applications and is widely used in autoclaves.

General Specifications

Thermocouple Type	Type K
Temperature Measurement Range	+250°C
Construction	Terminated with a miniature flat pin plug
Measuring Junction	Exposed
Standards Met	IEC
Application	Fast response, welded exposed junction

Mechanical Specifications

Termination	Miniature Plug
Length	0.3m (0.98ft)
Cable Insulation	1/0.376mm PTFE Flat Pair

Approvals

Declarations	RoHS
--------------	------

Similar Products

Colour Code	Type	Style	Cable Size	Length	Termination	RS Stock#
IEC	K	PTFE	1/0.376mm	0.3m (0.98ft)	Miniature Plug	0652763
IEC	K	PTFE	1/0.376mm	1m (3.3ft)	Miniature Plug	8722635
IEC	K	PTFE	1/0.376mm	2m (6.56ft)	Miniature Plug	8722638
IEC	K	PTFE	1/0.376mm	3m (9.84ft)	Miniature Plug	2209509
IEC	K	PTFE	1/0.376mm	5m (16.4 ft)	Miniature Plug	8722632
IEC	K	PTFE	1/0.376mm	10m (32.8ft)	Miniature Plug	8722641
IEC	T	PTFE	1/0.376mm	0.3m (0.98ft)	Miniature Plug	0652764
IEC	T	PTFE	1/0.376mm	1m (3.3ft)	Miniature Plug	8722644
IEC	T	PTFE	1/0.376mm	2m (6.56ft)	Miniature Plug	8722648
IEC	T	PTFE	1/0.376mm	3m (9.84ft)	Miniature Plug	2209510
IEC	T	PTFE	1/0.376mm	5m (16.4 ft)	Miniature Plug	8722657
IEC	T	PTFE	1/0.376mm	10m (32.8ft)	Miniature Plug	8722650