

Features

- USB-C Male
- Mini Displayport Female
- Active Adapter
- Supports 8K @ 30Hz

RS PRO USB-C to Mini DisplayPort Adapter

RS Stock No.: 0839493



RS Professionally Approved Products bring to you, professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This product is a Type-C to Mini DisplayPort Adapter. It allows you to connect a Type-C source or Thunderbolt TM 3 source to a Mini DisplayPort display at a maximum resolution of 8k@30Hz. It supports all DP Alt mode Type-C hosts. DP Alt mode is required to transmit both video and data via the USB C port.

- *Supports DisplayPort 1.4/1.2 Alt mode*
- *Supports per lane data rates of 8.1Gbps(HBR3), 5.4Gbps (HBR2), 2.7Gbps (HBR) and 1.62Gbps (RBR)*
- *Support up to 48 bit (16bit per channel) deep color*

General Specifications


Connector A	USB-C
Connector A Gender	Male
Connector B	Mini DisplayPort
Connector B Gender	Female
Maximum Resolution	7680x4320@30Hz
HDCP Support	v2.2, v1.4

Approvals

Standards Met	CE UKCA ROHS REACH
---------------	--------------------

Similar Products

Stock No.	Brand	Product Name
0839461	RS PRO	USB-C to 3.5mm audio adapter with PD - Black
0839462	RS PRO	USB-C to 3.5mm audio adapter with PD - Silver
USB3C-35AUDSP	RS PRO	USB-C to 3.5mm audio splitter cable
0839465	RS PRO	USB-C to 2.5Gbps Ethernet adapter
USB3C-ETHGHUBA	RS PRO	USB-C to 3x USB3.0 Hub with Gigabit RJ45
0839467	RS PRO	USB-C to HDMI (F) adapter
0839468	RS PRO	USB-C to HDMI adapter with PD
0839488	RS PRO	USB-C to HDMI, USB & Gigabit adapter with PD
0839489	RS PRO	USB-C to HDMI / USB-A x2 /SD / TF with DP1.4 Alt mode
0839490	RS PRO	USB-C to HDMI & USB adapter with PD
0839491	RS PRO	USB-C to HDMI and VGA adapter
0839492	RS PRO	USB-C to HDMI, DVI and VGA
0839493	RS PRO	USB C to Mini DisplayPort adapter



6	USB TYPE-C~34AWG+28AWG~Clamp	1	pcs
5	45P White PVC	8	g
4	Block Hood~ABS~white	1	pcs
3	Integrative shell~~ABS~white~	1	pcs
2	PCB+SMT	1	pcs
1	USB3.1Type CM TO CM~34AWG~ OD:3.9MM~ L=0.3M~ white~Nickel plating~ABS shell	1/2	pcs
NO	DESCRIPTION	Q'TY	UNIT

