

Side panel, PrismaSeT G, for extension enclosure H 650mm (11M), IP55, set of 2 (left/right)

LVS08353

EAN Code: 3606481884626

Main

Range	PrismaSeT	
Range of product	PrismaSeT G	
Product or component type	Side panel	
Range compatibility	PrismaSeT PrismaSeT G enclosure	
Device application	Low voltage electrical distribution	
Enclosure type	Metal enclosure	
installation description	Wall-mounted enclosure - width 600 mm	
Kit composition	2 side panel	
Number of vertical modules [50 mm]	11	
Standards	IEC 61439-1 for enclosure IEC 61439-2 for enclosure	
Product certifications	ASTA	

Complementary

Material	Treated sheet steel	
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder	
Surface finish	Textured Matt	
Colour	White (RAL 9003)	
Special colour options	Yes	
Width	250 mm	
Height	650 mm	
Net weight	4.24 kg	
Quantity per set	Set of 1	

Environment

IP degree of protection	IP55 for enclosure	
IK degree of protection	IK10	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm

Package 1 Width	23.0 cm
Package 1 Length	64.0 cm
Package 1 Weight	4.457 kg
Unit Type of Package 2	P12
Number of Units in Package 2	6
Package 2 Height	29.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	39.0 kg

Logistical informations

Country of origin FR

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability

Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better


Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
Halogen content performance	Halogen free plastic parts product
PVC free	Yes

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions



- All dimensions are approximate and are in
 Also see technical documentation.