

Chemical-protective suit with a multi-layer barrier, for robust protection against various hazards.

- **Reinforced protection:** The AlphaTec® 3000 Ultrasonically Welded & Taped - Model 111 protective suit's multi-layered fabric offers a robust barrier against various biohazards and inorganic chemicals
- **Enhanced features:** This protective barrier is bolstered by the inclusion of dual-zip systems, double cuffs and a double zip enclosure that boosts wear life
- **Increased visibility:** Designed in a high-visibility bright yellow color, this protective outer garment remains noticeable even in low-lit environments, boosting wearer and workplace safety
- **Assured antistatic properties:** In addition, it adheres to EN 1149-5 antistatic standards

*CE Category III Type 3/4/5/6 protection



Industries

- Chemical
- Mining
- Energy
- Life Sciences
- Food Processing
- Automotive Aftermarket
- Utilities

Applications

- Transferring liquids and solids between vessels and tanks and process equipment
- Unexpected leakages spills or other releases
- Opening and draining pumps valves or lines
- Loading and unloading trucks and vehicles
- Filling, blending and charging of raw materials
- Product inspection
- Mixing or loading chemicals
- Cleaning of plant and machines

KEY FEATURES & BENEFITS

- **Lightweight multi-layer barrier:** Protection against chemical hazards
- **Double cuffs and dual-zip systems:** Increased wear life
- **Bright yellow high-visibility exterior:** Greater workplace safety

Technology



MICROCHEM™
Chemical Barrier Technology


Material Diagram




External film barrier layer

Core high barrier film layer

Non-woven inner layer



Seam Diagram



Performance Standards



EN ISO 13688:2013

Product Information

Product Information	
Available Sizes	S, M, L, XL, 2XL, 3XL, 4XL, 5XL
Color	Yellow
Country Of Origin	China
Packaging Overview	Individually packaged
Product Material	Multi-layer non-woven barrier Laminate fabric
Product Reference	3000 - Model 111 WT
Standards Overview	CE CATEGORY III (Type 3-B, Type 4-B, Type 5-B, Type 6-B, EN 1073-2, EN 14126, EN 1149-5)
Seam Type	Welded and Taped
Shelf Life	5 years
Style Number	Y30T111

Suit components & accessories

Suit Components and Accessories	
Design Features	Coverall with 2-piece hood, double zip closure, double cuffs, elasticated hood, waist, double cuffs and ankles.

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444

Australia
Ansell Limited
T: +61 1800 337 041

Asia Pacific Region
Ansell Global Trading Center
T: +603 8310 6688

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

