

Features

- ESD – Designed to safely discharge static electricity and protect electronic components from electrostatic discharge events.
- Available in different sizes

RS PRO ESD Worktable 1500x700, 1500x800, 1500x900 L-type - electric height

RS Stock No.: 0687767, 0687768, 0687769



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Light Duty System – Electric Height Adjustable ESD Workstation

The Light Duty System is a modern and ergonomic workstation designed for light-duty tasks in environments where comfort, precision, and adjustability are essential. Equipped with electric height adjustment from 700 to 1150 mm and dual column actuators, it allows users to personalize the workstation to their needs, improving posture and reducing fatigue. The intuitive DPG control panel and integrated collision detection sensor ensure safe and user-friendly operation.

Constructed from high-quality structural steel with TIG-welded joints, the system offers long-term durability and a standard load capacity of 150 kg. It is fully adaptable for electrostatic discharge (ESD) protection, meeting PN-EN 61340-5-1:2017 standards, and complies with PN-EN ISO 9001:2015 quality requirements.

The 25 mm thick tabletop, resistant to wear and temperatures up to 50°C, features a light gray RAL 7035 finish with a 1 mm dark gray ABS edge, combining durability with modern design. The workstation's modular design enables easy connection with additional units and accessories, making it suitable for light manufacturing, electronics, workshops, and laboratory applications.

General Specifications

WIDTH (mm)	1500
DEPTH (mm)	800
WEIGHT (kg)	73
MAX LOAD (kg)	150
ESD	YES
COLOUR	RAL 7035 (LIGHT GREY) RAL 9005 (BLACK)
MATERIAL OF TABLE FRAME	CONSTRUCTION STEEL
TABLETOP	DOUBLE SIDED ANTISTATIC, DISSIPATIVE, WITH GRAPHITE ADDITIVE, COVERED WITH A MELAMINE LAYER, THICKNESS 25 mm
TYPE OF GLIDES	SELF-LEVELLING
RESISTANCE GROUNDING (0hm)	$10^4 - 10^8$

Available in the following versions:

Stock No.	Brand	Product Name	Width	Depth
0687767	RS PRO	ESD worktable 1500x700, L-type, electric height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	1500	700
0687768	RS PRO	ESD worktable 1500x800, L-type, electric height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	1500	800
0687769	RS PRO	ESD worktable 1500x900, L-type, electric height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	1500	900

Similar Products

Stock No.	Brand	Product Name	Width	Depth
0687732	RS PRO	ESD worktable 1200x700, L-type, electric height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	1200	700
0687661	RS PRO	ESD worktable 1800x700, L-type, electric height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	1800	700
0687686	RS PRO	ESD worktable 2000x700, L-type, electric height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	2000	700
0687735	RS PRO	ESD worktable 1200x700, L-type, electric height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	1200	700
0687771	RS PRO	ESD worktable 1500x700, L-type, electric height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	1500	700
0687665	RS PRO	ESD worktable 1800x700, L-type, electric height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	1800	700

0687689	RS PRO	ESD worktable 2000x700, L-type, electric height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	2000	700
---------	--------	---	------	-----