

Features

- Euro Module
- USB 3.0 Type A
- USB 3.0 Type B
- 50mm x 25mm
- White
- Pigtail Type
- Gold Connector

RS PRO USB 3.0 Type A –B Euro Module – Pigtail Type

RS Stock No.: 0839429



RS Professionally Approved Products bring to you, professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The USB 3.0 A Type module is a 50mm x 25mm clip in Euro Module.

The pigtail is a USB Type A (F) to USB Type B (F) allowing you to connect a standard male cable to the other side easily. This module will clip into any euro mod faceplate be it single gang or dual gang.

General Specifications


Size	25mm
Number Of Connections	1
Type Of Connection	USB 3.0 A Type & B Type
Gender	Female
Dimensions	50mm x 25mm

Approvals

Declarations	CE UKCA ROHS REACH WEEE
Standards Met	CE UKCA ROHS REACH WEEE
UL	Made using UL2725 Cable

Similar Products

Stock No.	Brand	Product Name	Length	Dimensions	Colour
AV-MODHDMI	RS PRO	HDMI Euro Mod	15cm Pigtail	50mm x 25mm	White
AV-MODSVGA	RS PRO	SVGA Euro Mod	15cm Pigtail	50mm x 25mm	White
AV-MOD2RCA	RS PRO	2 X RCA Euro Mod	Coupler Style	50mm x 25mm	White
AV-MODUSBB	RS PRO	USB B Euro Mod	15cm Pigtail	50mm x 25mm	White
AV-MOD3TRS	RS PRO	3.5mm Euro Mod	15cm Pigtail	50mm x 25mm	White
AV-MOD2FCONN	RS PRO	2 X F Con Euro Mod	Coupler Style	50mm x 25mm	White
0839428	RS PRO	USB 3.0 AF Euro Mod	15cm Pigtail	50mm x 25mm	White



[(7/0.127TC*1P+D7/0.10TC+AL+MYALR)*2C+7/0.127TC*1P+7/0.20*2C+AL-FOIL
+D(1/0.32BC)+B(128/0.12AL-M6)] Black PVC, OD:Ø5.5±0.2M

PIN OUT	
USB A(M)	USB B(M)
1 — RED	1
2 — WHITE	2
3 — GREEN	3
4 — BLACK	4
5 — BLUE	5
6 — YELLOW	6
7 — DRAIN WIRE	7
8 — PURPLE	8
9 — ORANGE	9
SHELL — BRAID	SHELL