




## DISTRIBUTOR STOCKING ITEMS

- Inventory Support
- Standard Packages
- Lowest Pricing
- Fox Quality
- Technical Support



• FOX STANDARD SPECIFICATIONS						
PARAMETER	F1100E	F5C-2E	H5C-2E	F3345	F4100	F4105/F4106
Voltage	5V	5V	5V	5V	3.3V	3.3V
Frequency Stability	±100PPM	±100PPM	±100PPM	±100PPM	±100PPM	±50 / ±25PPM
Operating Temperature Range	0°C ~ +70°C	0°C ~ +70°C	0°C ~ +70°C	-10°C ~ +70°C	-10°C ~ +70°C	-10°C ~ +70°C
Output	TTL	HCMOS	HCMOS	HCMOS	HCMOS	HCMOS

FREQUENCY (MHz)	F1100E	F5C-2E	H5C-2E	F3345	F4100	F4105 /F4106	JITO-2
1.000000	F1100E-010		H5C2E-010				JITO-2
1.843200	F1100E-018			F3345-018	F4100-018		JITO-2
2.000000	F1100E-020						JITO-2
2.457600	F1100E-024						JITO-2
3.686400	F1100E-0368		H5C2E-0368		F4100-0368		JITO-2
4.000000	F1100E-040				F4100-040		JITO-2
6.000000	F1100E-060						JITO-2
7.372800	F1100E-073						JITO-2
8.000000	F1100E-080	F5C2E-080	H5C2E-080	F3345-080			JITO-2
10.000000	F1100E-100	F5C2E-100			F4100-100		JITO-2
11.059200	F1100E-115						JITO-2
12.000000	F1100E-120	F5C2E-120		F3345-120			JITO-2
14.318180	F1100E-143			F3345-143	F4100-143	F4105-143	JITO-2
14.745600	F1100E-147						JITO-2
16.000000	F1100E-160	F5C2E-160	H5C2E-160	F3345-160	F4100-160		JITO-2
18.432000	F1100E-184				F4100-184		JITO-2
20.000000	F1100E-200	F5C2E-200	H5C2E-200	F3345-200	F4100-200	F4105-200	JITO-2
24.000000	F1100E-240	F5C2E-240		F3345-240			JITO-2
25.000000	F1100E-250	F5C2E-250	H5C2E-250	F3345-250	F4100-250	F4105-250	JITO-2
32.000000	F1100E-320	F5C2E-320	H5C2E-320	F3345-320	F4100-320	F4105-320	JITO-2
33.333000					F4100-333		JITO-2
40.000000	F1100E-400	F5C2E-400	H5C2E-400	F3345-400	F4100-400	F4105-400	JITO-2
44.000000						F4106-440	JITO-2
48.000000	F1100E-480				F4100-480		JITO-2
50.000000	F1100E-500		H5C2E-500	F3345-500	F4100-500	F4105-500	JITO-2
60.000000				F3345-600	F4100-600		JITO-2
64.000000	F1100E-640		H5C2E-640	F3345-640			JITO-2
66.666700					F4100-666	F4105-666	JITO-2
80.000000	F1100E-800						JITO-2
100.000000	F1100E-1000					F4105-1000	JITO-2
106.250000					F4100-1062	F4105-1062	JITO-2
125.000000						F4105-1250	JITO-2

Rev. 6/04