

A927 Series Drills Specification

| Part No. | Description | Material | Finish | Flute Length | Overall Length | Manf. Dia. |
|------------|-------------------------|----------|--------|--------------|----------------|------------|
| A927*1.0 | PFX Drills, Stub Length | HSCo | BRIGHT | 6 | 26 | 1 |
| A927*1.1 | PFX Drills, Stub Length | HSCo | BRIGHT | 7 | 28 | 1.1 |
| A927*1.2 | PFX Drills, Stub Length | HSCo | BRIGHT | 8 | 30 | 1.2 |
| A927*1.3 | PFX Drills, Stub Length | HSCo | BRIGHT | 8 | 30 | 1.3 |
| A927*1.4 | PFX Drills, Stub Length | HSCo | BRIGHT | 9 | 32 | 1.4 |
| A927*1.5 | PFX Drills, Stub Length | HSCo | BRIGHT | 9 | 32 | 1.5 |
| A927*1/16 | PFX Drills, Stub Length | HSCo | BRIGHT | 10 | 34 | 1.59 |
| A927*1.6 | PFX Drills, Stub Length | HSCo | BRIGHT | 10 | 34 | 1.6 |
| A927*1.7 | PFX Drills, Stub Length | HSCo | BRIGHT | 10 | 34 | 1.7 |
| A927*1.8 | PFX Drills, Stub Length | HSCo | BRIGHT | 11 | 36 | 1.8 |
| A927*1.9 | PFX Drills, Stub Length | HSCo | BRIGHT | 11 | 36 | 1.9 |
| A927*5/64 | PFX Drills, Stub Length | HSCo | BRIGHT | 12 | 38 | 1.98 |
| A927*2.0 | PFX Drills, Stub Length | HSCo | BRIGHT | 12 | 38 | 2 |
| A927*2.1 | PFX Drills, Stub Length | HSCo | BRIGHT | 12 | 38 | 2.1 |
| A927*2.2 | PFX Drills, Stub Length | HSCo | BRIGHT | 13 | 40 | 2.2 |
| A927*2.3 | PFX Drills, Stub Length | HSCo | BRIGHT | 13 | 40 | 2.3 |
| A927*3/32 | PFX Drills, Stub Length | HSCo | BRIGHT | 14 | 43 | 2.38 |
| A927*2.4 | PFX Drills, Stub Length | HSCo | BRIGHT | 14 | 43 | 2.4 |
| A927*2.5 | PFX Drills, Stub Length | HSCo | BRIGHT | 14 | 43 | 2.5 |
| A927*2.6 | PFX Drills, Stub Length | HSCo | BRIGHT | 14 | 43 | 2.6 |
| A927*2.7 | PFX Drills, Stub Length | HSCo | BRIGHT | 16 | 46 | 2.7 |
| A927*7/64 | PFX Drills, Stub Length | HSCo | BRIGHT | 16 | 46 | 2.78 |
| A927*2.8 | PFX Drills, Stub Length | HSCo | BRIGHT | 16 | 46 | 2.8 |
| A927*2.9 | PFX Drills, Stub Length | HSCo | BRIGHT | 16 | 46 | 2.9 |
| A927*3.0 | PFX Drills, Stub Length | HSCo | BRIGHT | 16 | 46 | 3 |
| A927*3.1 | PFX Drills, Stub Length | HSCo | BRIGHT | 18 | 49 | 3.1 |
| A927*1/8 | PFX Drills, Stub Length | HSCo | BRIGHT | 18 | 49 | 3.18 |
| A927*3.2 | PFX Drills, Stub Length | HSCo | BRIGHT | 18 | 49 | 3.2 |
| A927*3.3 | PFX Drills, Stub Length | HSCo | BRIGHT | 18 | 49 | 3.3 |
| A927*3.4 | PFX Drills, Stub Length | HSCo | BRIGHT | 20 | 52 | 3.4 |
| A927*3.5 | PFX Drills, Stub Length | HSCo | BRIGHT | 20 | 52 | 3.5 |
| A927*9/64 | PFX Drills, Stub Length | HSCo | BRIGHT | 20 | 52 | 3.57 |
| A927*3.6 | PFX Drills, Stub Length | HSCo | BRIGHT | 20 | 52 | 3.6 |
| A927*3.7 | PFX Drills, Stub Length | HSCo | BRIGHT | 20 | 52 | 3.7 |
| A927*3.8 | PFX Drills, Stub Length | HSCo | BRIGHT | 22 | 55 | 3.8 |
| A927*3.9 | PFX Drills, Stub Length | HSCo | BRIGHT | 22 | 55 | 3.9 |
| A927*5/32 | PFX Drills, Stub Length | HSCo | BRIGHT | 22 | 55 | 3.97 |
| A927*4.0 | PFX Drills, Stub Length | HSCo | BRIGHT | 22 | 55 | 4 |
| A927*4.1 | PFX Drills, Stub Length | HSCo | BRIGHT | 22 | 55 | 4.1 |
| A927*4.2 | PFX Drills, Stub Length | HSCo | BRIGHT | 22 | 55 | 4.2 |
| A927*4.3 | PFX Drills, Stub Length | HSCo | BRIGHT | 24 | 58 | 4.3 |
| A927*11/64 | PFX Drills, Stub Length | HSCo | BRIGHT | 24 | 58 | 4.37 |
| A927*4.4 | PFX Drills, Stub Length | HSCo | BRIGHT | 24 | 58 | 4.4 |
| A927*4.5 | PFX Drills, Stub Length | HSCo | BRIGHT | 24 | 58 | 4.5 |
| A927*4.6 | PFX Drills, Stub Length | HSCo | BRIGHT | 24 | 58 | 4.6 |
| A927*4.7 | PFX Drills, Stub Length | HSCo | BRIGHT | 24 | 58 | 4.7 |
| A927*3/16 | PFX Drills, Stub Length | HSCo | BRIGHT | 26 | 62 | 4.76 |
| A927*4.8 | PFX Drills, Stub Length | HSCo | BRONZE | 26 | 62 | 4.8 |
| A927*4.9 | PFX Drills, Stub Length | HSCo | BRIGHT | 26 | 62 | 4.9 |

A927 Series Drills Specification

| Part No. | Description | Material | Finish | Flute Length | Overall Length | Manf. Dia. |
|------------|-------------------------|----------|--------|--------------|----------------|------------|
| A927*5.0 | PFX Drills, Stub Length | HSCo | BRIGHT | 26 | 62 | 5 |
| A927*5.1 | PFX Drills, Stub Length | HSCo | BRIGHT | 26 | 62 | 5.1 |
| A927*13/64 | PFX Drills, Stub Length | HSCo | BRIGHT | 26 | 62 | 5.16 |
| A927*5.2 | PFX Drills, Stub Length | HSCo | BRIGHT | 26 | 62 | 5.2 |
| A927*5.3 | PFX Drills, Stub Length | HSCo | BRIGHT | 26 | 62 | 5.3 |
| A927*5.4 | PFX Drills, Stub Length | HSCo | BRIGHT | 28 | 66 | 5.4 |
| A927*5.5 | PFX Drills, Stub Length | HSCo | BRIGHT | 28 | 66 | 5.5 |
| A927*7/32 | PFX Drills, Stub Length | HSCo | BRIGHT | 28 | 66 | 5.56 |
| A927*5.6 | PFX Drills, Stub Length | HSCo | BRIGHT | 28 | 66 | 5.6 |
| A927*5.7 | PFX Drills, Stub Length | HSCo | BRIGHT | 28 | 66 | 5.7 |
| A927*5.8 | PFX Drills, Stub Length | HSCo | BRIGHT | 28 | 66 | 5.8 |
| A927*5.9 | PFX Drills, Stub Length | HSCo | BRIGHT | 28 | 66 | 5.9 |
| A927*15/64 | PFX Drills, Stub Length | HSCo | BRIGHT | 28 | 66 | 5.95 |
| A927*6.0 | PFX Drills, Stub Length | HSCo | BRIGHT | 28 | 66 | 6 |
| A927*6.1 | PFX Drills, Stub Length | HSCo | BRIGHT | 31 | 70 | 6.1 |
| A927*6.2 | PFX Drills, Stub Length | HSCo | BRIGHT | 31 | 70 | 6.2 |
| A927*6.3 | PFX Drills, Stub Length | HSCo | BRIGHT | 31 | 70 | 6.3 |
| A927*1/4 | PFX Drills, Stub Length | HSCo | BRIGHT | 31 | 70 | 6.35 |
| A927*6.4 | PFX Drills, Stub Length | HSCo | BRIGHT | 31 | 70 | 6.4 |
| A927*6.5 | PFX Drills, Stub Length | HSCo | BRIGHT | 31 | 70 | 6.5 |
| A927*6.6 | PFX Drills, Stub Length | HSCo | BRIGHT | 31 | 70 | 6.6 |
| A927*6.7 | PFX Drills, Stub Length | HSCo | BRIGHT | 31 | 70 | 6.7 |
| A927*17/64 | PFX Drills, Stub Length | HSCo | BRIGHT | 34 | 74 | 6.75 |
| A927*6.8 | PFX Drills, Stub Length | HSCo | BRIGHT | 34 | 74 | 6.8 |
| A927*6.9 | PFX Drills, Stub Length | HSCo | BRIGHT | 34 | 74 | 6.9 |
| A927*7.0 | PFX Drills, Stub Length | HSCo | BRIGHT | 34 | 74 | 7 |
| A927*7.1 | PFX Drills, Stub Length | HSCo | BRIGHT | 34 | 74 | 7.1 |
| A927*9/32 | PFX Drills, Stub Length | HSCo | BRIGHT | 34 | 74 | 7.14 |
| A927*7.2 | PFX Drills, Stub Length | HSCo | BRIGHT | 34 | 74 | 7.2 |
| A927*7.3 | PFX Drills, Stub Length | HSCo | BRIGHT | 34 | 74 | 7.3 |
| A927*7.4 | PFX Drills, Stub Length | HSCo | BRIGHT | 34 | 74 | 7.4 |
| A927*7.5 | PFX Drills, Stub Length | HSCo | BRIGHT | 34 | 74 | 7.5 |
| A927*19/64 | PFX Drills, Stub Length | HSCo | BRIGHT | 37 | 79 | 7.54 |
| A927*7.6 | PFX Drills, Stub Length | HSCo | BRIGHT | 37 | 79 | 7.6 |
| A927*7.7 | PFX Drills, Stub Length | HSCo | BRIGHT | 37 | 79 | 7.7 |
| A927*7.8 | PFX Drills, Stub Length | HSCo | BRIGHT | 37 | 79 | 7.8 |
| A927*7.9 | PFX Drills, Stub Length | HSCo | BRIGHT | 37 | 79 | 7.9 |
| A927*5/16 | PFX Drills, Stub Length | HSCo | BRIGHT | 37 | 79 | 7.94 |
| A927*8.0 | PFX Drills, Stub Length | HSCo | BRIGHT | 37 | 79 | 8 |
| A927*8.1 | PFX Drills, Stub Length | HSCo | BRIGHT | 37 | 79 | 8.1 |
| A927*8.2 | PFX Drills, Stub Length | HSCo | BRIGHT | 37 | 79 | 8.2 |
| A927*8.3 | PFX Drills, Stub Length | HSCo | BRIGHT | 37 | 79 | 8.3 |
| A927*21/64 | PFX Drills, Stub Length | HSCo | BRIGHT | 37 | 79 | 8.33 |
| A927*8.4 | PFX Drills, Stub Length | HSCo | BRIGHT | 37 | 79 | 8.4 |
| A927*8.5 | PFX Drills, Stub Length | HSCo | BRIGHT | 37 | 79 | 8.5 |
| A927*8.6 | PFX Drills, Stub Length | HSCo | BRIGHT | 40 | 84 | 8.6 |
| A927*8.7 | PFX Drills, Stub Length | HSCo | BRIGHT | 40 | 84 | 8.7 |
| A927*11/32 | PFX Drills, Stub Length | HSCo | BRIGHT | 40 | 84 | 8.73 |
| A927*8.8 | PFX Drills, Stub Length | HSCo | BRIGHT | 40 | 84 | 8.8 |

A927 Series Drills Specification

| Part No. | Description | Material | Finish | Flute Length | Overall Length | Manf. Dia. |
|------------|-------------------------|----------|--------|--------------|----------------|------------|
| A927*8.9 | PFX Drills, Stub Length | HSCo | BRIGHT | 40 | 84 | 8.9 |
| A927*9.0 | PFX Drills, Stub Length | HSCo | BRIGHT | 40 | 84 | 9 |
| A927*9.1 | PFX Drills, Stub Length | HSCo | BRIGHT | 40 | 84 | 9.1 |
| A927*23/64 | PFX Drills, Stub Length | HSCo | BRIGHT | 40 | 84 | 9.13 |
| A927*9.2 | PFX Drills, Stub Length | HSCo | BRIGHT | 40 | 84 | 9.2 |
| A927*9.3 | PFX Drills, Stub Length | HSCo | BRIGHT | 40 | 84 | 9.3 |
| A927*9.4 | PFX Drills, Stub Length | HSCo | BRIGHT | 40 | 84 | 9.4 |
| A927*9.5 | PFX Drills, Stub Length | HSCo | BRIGHT | 40 | 84 | 9.5 |
| A927*3/8 | PFX Drills, Stub Length | HSCo | BRIGHT | 43 | 89 | 9.53 |
| A927*9.6 | PFX Drills, Stub Length | HSCo | BRIGHT | 43 | 89 | 9.6 |
| A927*9.7 | PFX Drills, Stub Length | HSCo | BRIGHT | 43 | 89 | 9.7 |
| A927*9.8 | PFX Drills, Stub Length | HSCo | BRIGHT | 43 | 89 | 9.8 |
| A927*9.9 | PFX Drills, Stub Length | HSCo | BRIGHT | 43 | 89 | 9.9 |
| A927*25/64 | PFX Drills, Stub Length | HSCo | BRIGHT | 43 | 89 | 9.92 |
| A927*10.0 | PFX Drills, Stub Length | HSCo | BRIGHT | 43 | 89 | 10 |
| A927*10.2 | PFX Drills, Stub Length | HSCo | BRIGHT | 43 | 89 | 10.2 |
| A927*10.3 | PFX Drills, Stub Length | HSCo | BRIGHT | 43 | 89 | 10.3 |
| A927*13/32 | PFX Drills, Stub Length | HSCo | BRIGHT | 43 | 89 | 10.32 |
| A927*10.4 | PFX Drills, Stub Length | HSCo | BRIGHT | 43 | 89 | 10.4 |
| A927*10.5 | PFX Drills, Stub Length | HSCo | BRIGHT | 43 | 89 | 10.5 |
| A927*27/64 | PFX Drills, Stub Length | HSCo | BRIGHT | 50 | 95 | 10.72 |
| A927*10.8 | PFX Drills, Stub Length | HSCo | BRIGHT | 50 | 95 | 10.8 |
| A927*11.0 | PFX Drills, Stub Length | HSCo | BRIGHT | 50 | 95 | 11 |
| A927*7/16 | PFX Drills, Stub Length | HSCo | BRIGHT | 50 | 95 | 11.11 |
| A927*11.2 | PFX Drills, Stub Length | HSCo | BRIGHT | 50 | 95 | 11.2 |
| A927*11.5 | PFX Drills, Stub Length | HSCo | BRIGHT | 50 | 95 | 11.5 |
| A927*29/64 | PFX Drills, Stub Length | HSCo | BRIGHT | 50 | 95 | 11.51 |
| A927*11.8 | PFX Drills, Stub Length | HSCo | BRIGHT | 50 | 95 | 11.8 |
| A927*15/32 | PFX Drills, Stub Length | HSCo | BRIGHT | 57 | 102 | 11.91 |
| A927*12.0 | PFX Drills, Stub Length | HSCo | BRIGHT | 57 | 102 | 12 |
| A927*12.2 | PFX Drills, Stub Length | HSCo | BRIGHT | 57 | 102 | 12.2 |
| A927*31/64 | PFX Drills, Stub Length | HSCo | BRIGHT | 57 | 102 | 12.3 |
| A927*12.5 | PFX Drills, Stub Length | HSCo | BRIGHT | 57 | 102 | 12.5 |
| A927*1/2 | PFX Drills, Stub Length | HSCo | BRIGHT | 57 | 102 | 12.7 |
| A927*12.8 | PFX Drills, Stub Length | HSCo | BRONZE | 57 | 102 | 12.8 |
| A927*13.0 | PFX Drills, Stub Length | HSCo | BRIGHT | 57 | 102 | 13 |