

6006 Joker XS/S Self-setting double spanner, 7; 8; 9; 10 x 1/4; 5/16; 3/8" x 10; 11;  
12; 13 x 7/16; 1/2" x 161 mm  
6006 Joker Self-setting double spanner



<b>EAN:</b>	4013288233288	<b>Size:</b>	155x55x13 mm
<b>Part number:</b>	05020330001	<b>Weight:</b>	130 g
<b>Article number:</b>	6006 Joker XS/S	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82041100

- Self-setting double spanner
- For hexagon screw heads and bolts with wrench sizes 7.0; 8.0; 9.0; 10.0; 11.0; 12.0; 13.0 (metric)
- For hexagon screw heads and bolts with wrench sizes 1/4"; 5/16"; 3/8"; 7/16"; 1/2" (imperial)
- Automatically and continuously gripping hexagon screws and bolts
- Lever mechanism upon gripping prevents slipping and damage
- With mechanical ratchet functionality for fast and consistent screwdriving without removing the spanner
- Return angle of only 30° when using the corner-width rectangular prisms in the jaw

Self-setting double spanner for hexagon screw heads and bolts with wrench sizes 7-10 and 10-13 (metric) or 1/4"-3/8" and 7/16"-1/2" (imperial). With its continuous and parallel jaws, the tool replaces several single spanner sizes. The required size is automatically and continuously set when attaching the tool to the hexagon bolt or screw. The integrated lever mechanism securely clamps the hexagon screw or bolt between the jaws, which significantly reduces the risk of slippage or damage. The ratchet feature ensures fast and consistent screwdriving without removing the tool. By using the corner-width rectangular prisms, a return angle of only 30° can be achieved. Ratchet feature and corner-width prism make it possible to work even in confined spaces. The adjustable Joker 6006 double spanner with ratchet functionality is the universal screwdriving tool. Self-setting. Gripping. Spanning.




#### Web link

<https://www.wera.de/en/05020330001>

Wera - 6006 Joker XS/S  
05020330001 - 4013288233288


Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

Joker 6006: automatically and continuously self-setting




With its automatically and continuously gripping parallel jaws, the Joker 6006 double spanner covers all dimensions within the potential operative range. The tool finds the required size by itself when attaching it to the bolt or screw.

Joker 6006: gentle to the screw




The parallel, smooth jaws of the Joker 6006 double spanner offer a seating stress and can thus prevent the nut or screw head from rounding, which can occur when power is transmitted over corners.

Joker 6006: ratchet mechanism for quick working










The ratchet functionality in both jaws of the double spanner ensures fast and consistent screwdriving without removing the tool.

Joker 6006: low return angle



Thanks to the corner-width rectangular prisms in both jaws of the double spanner, a return angle of only 30° can be achieved.

Further versions in this product family:

	 mm	 inch	 mm	 inch	 mm	 mm	 mm
05020330001	7.0; 8.0; 9.0; 10.0	1/4"; 5/16"; 3/8"	10.0; 11.0; 12.0; 13.0	7/16"; 1/2"	8.0	10.0	161.0