



Visit the website for your country to get more information and discover our products.

India

Proceed

HellermannTyton

09/07/2026

Spare part, 8pc. (SP_EVO_cut_nosepiece_set)

Art.-No. 110-05095 | SP_EVO_cut_nosepiece_set-PA66GF30-BU |

 [Copy item description](#)



- Nosepiece set for EVO cut tool includes eight interchangeable nosepieces
- 3 nosepieces for cutting different cable tie strap widths
- 3 nosepieces for cutting different sizes of cable tie heads
- 2 nosepieces for cutting KR6 and KR8 ties
-
-

[Show more](#)

RoHS





Visit the website for your country to get more information and discover our products.

[Proceed](#)

HellermannTyton

09/07/2026

Base Data

Application	This is the nosepiece set for the EVO cut tool. The EVO cut is a cutting tool for plastic ties, which ensures the cut of the strap or head while preserving wires and harnesses from being damaged. This applies to flexible cables, bundles and lines as well as rigid bundled goods. Its use is recommended in many applications for which wires and harnesses have a high value added. Especially for sensitive cable harnesses the use of the EVO cut is recommended. The cutting tool is made of a lightweight plastic housing and an ergonomic, non-slip handle for a comfortable and secure grip. The nosepiece set includes eight interchangeable nosepieces for plastic cable ties and KR-Series ties of varying widths and thicknesses.
Colour	Blue (BU)
Material	Polyamide 6.6, glass-fibre reinforced (PA66GF30)
Operation	manual
PART DESCRIPTION	SP_EVO_cut_nosepiece_set-PA66GF30-BU
Package Content	8 pc.
Package Content packed in	box
Product Family	EVO cut
Product Group	Manual cutting tool for plastic ties
Short Description	EVO cut spare part nosepiece set
Tool property	Manual clipping
Tool suitable cable tie material	Plastic
Type	SP_EVO_cut_nosepiece_set
Weight/Unit	0.024 kg

Product Dimensions

Tension Setting	Manual
-----------------	--------



Visit the website for your country to get more information and discover our products.

[Proceed](#)

HellermannTyton

09/07/2026

ROHS compliant Yes

Specifications **RoHS** ✓

Logistics and Packaging

Country of Origin CN

Customs Number 82055980

GTIN-13 / EAN 4031026666419

More Information

ETIM 7.0 Key EC000453

ETIM 8.0 Key EC000453

ETIM 9.0 Key EC000453

UNSPSC Key 27112410

HellermannTyton

International

[Imprint](#)

[Policy and Values](#)

[Sitemap](#)

[Data Protection](#)

[Contact](#)



Visit the website for your country to get more information
and discover our products.

[Proceed](#)

HellermannTyton

09/07/2026

Social Media