

Datasheet

RS Stock No: 8229224

BZP Steel Hexagon Socket Button Head Screws: Metric Thread



Button Head Socket Screws are designed for light duty with a similar thread design as a Socket Cap Screw although the dome-shaped head is wider and has a lower profile than a Socket Cap Screw, presenting an aesthetic appearance to an assembly.

- Threaded in accordance with ISO 7380 Standard
- BZP Steel
- 10.9 grade High Tensile Steel
- Used for applications with limited space in high-tensile applications
- Suitable for light fastening applications in most food, facilities maintenance, electronic and domestic applications
- Typical applications include; Machine tooling, securing guards and covers, securing ornamental fixtures, plus man more engineering applications
- Requires a Hex Key / Allen Key



ENGLISH

Please view our full range listing below for all BZP Steel Hexagon Socket Button Head Screws:

Head Shape	Material	Thread Size	Length	RS Part No.
Socket Button	Steel BZP	M3	6 mm	8229155
Socket Button	Steel BZP	M4	6 mm	8229164
Socket Button	Steel BZP	M4	20 mm	8229167
Socket Button	Steel BZP	M4	25 mm	8229161
Socket Button	Steel BZP	M5	6 mm	8229170
Socket Button	Steel BZP	M5	8 mm	8229173
Socket Button	Steel BZP	M5	25 mm	8229177
Socket Button	Steel BZP	M5	35 mm	8229186
Socket Button	Steel BZP	M6	8 mm	8229189
Socket Button	Steel BZP	M6	10 mm	8229183
Socket Button	Steel BZP	M6	50 mm	8229192
Socket Button	Steel BZP	M8	10 mm	8229195
Socket Button	Steel BZP	M8	30 mm	8229199
Socket Button	Steel BZP	M8	35 mm	8229209
Socket Button	Steel BZP	M8	40 mm	8229202
Socket Button	Steel BZP	M8	45 mm	8229206
Socket Button	Steel BZP	M8	50 mm	8229215
Socket Button	Steel BZP	M10	16 mm	8229218
Socket Button	Steel BZP	M10	20 mm	8229212
Socket Button	Steel BZP	M10	25 mm	8229221
Socket Button	Steel BZP	M10	30 mm	8229224
Socket Button	Steel BZP	M10	35 mm	8229228
Socket Button	Steel BZP	M10	40 mm	8229237
Socket Button	Steel BZP	M10	50 mm	8229320



ENGLISH

Please view our full range listing below for all BZP Steel Hexagon Socket Button Head Screws:

Head Shape	Material	Thread Size	Length	RS Part No.
Socket Button	Steel BZP	M12	20 mm	8229234
Socket Button	Steel BZP	M12	25 mm	8229243
Socket Button	Steel BZP	M12	30 mm	8229246
Socket Button	Steel BZP	M12	35 mm	8229240
Socket Button	Steel BZP	M12	40 mm	8229259

