



# Shockguard Plus™ Ceiling Accessories



MK Electric offers a comprehensive range of white ceiling accessories for all requirements, included in the range are enhanced 'safety' lampholders.

Unlike most other 'safety' lampholders, when the lamp is removed it automatically shields the contact by means of a specially designed shutter and it remains that way until a lamp is replaced. This means that with no bulb in place there is no danger of electrocution from exposed contacts, as the contact pins are totally isolated.

#### **Ease of installation**

Pendant sets incorporate a heat resistant lampholder (1150 WHI), and ceiling rose with a transparent base and clear terminal markings for ease of identification. Terminals are grouped in line with, neutral, loop-in and earth terminals (1161 WHI).

#### **Safety**

Specially designed shutter automatically shields the lamp contacts, therefore eliminating the danger of electrocution.

#### **Reliability**


Shockguard Plus products are 100% tested before delivery for confidence a 'fit and forget' installation can be achieved. Fully compliant with the relevant British Standards BS7895 for bayonet lampholders with enhanced safety and BSEN 61184.

#### **Durability**

Manufactured from the highest quality materials to give a high gloss finish which is both scratch resistant and colour fade resistant.



DESIGNED FOR LIFE™



MK Ceiling Rose has a transparent base. Precut aperture



Pins are operated by a specially designed shutter and are only exposed when a lamp is in place. When the lampholder is not in use safety is guaranteed as the shutter ensures total isolation. The threat of user electrocution is eliminated

PRODUCT RANGE			
LIST NUMBER	DESCRIPTION	PRODUCT GROUP	OLD PART NUMBER
1146 WHI	Shockguard Plus 150mm Pendant set	Ceiling Accessories	1156WHI
1149 WHI	Shockguard Plus 230mm Pendant set	Ceiling Accessories	1159WHI
1150 WHI	Shockguard Plus pendant lampholder	Ceiling Accessories	1140WHI
1151 WHI	Shockguard Plus pendant lampholder HO	Ceiling Accessories	1141WHI
1152 WHI	Shockguard Plus angled batten holder	Ceiling Accessories	1142WHI
1154 WHI	Shockguard Plus batten holder	Ceiling Accessories	1144WHI
TECHNICAL			
PRODUCT SPECIFICATION			
Rated Voltage	250Vac 50Hz		
Flex	0.75mm <sup>2</sup> heat resistant PVC		
Max Cont. Load (Max weight suspended from pendant lampholder)	3Kg		

MK



Novar ED&S Ltd The Arnold Centre Paycocke Road Basildon Essex SS14 3EA United Kingdom		Technical Helpline Tel 01268 563256
Customer Service Tel 01268 563000	Customer Service Fax 01268 563563	Literature Helpline Tel 0870 240 3385
E-mail mk_orderenquiries@novar.com	E-mail mk_technical@novar.com	Website www.mkelectric.co.uk
Registered office: Novar House 24 Queens Road Weybridge Surrey KT13 9UX Registered No. 189291		Literature Ref: ShockG MK/03-09-01/010

MK is a Novar business

