



ARENAL S3S SR

UTILITIES

Robust and comfortable low-cut shoe, adapted to more difficult environments.

Foot protection



Specific benefits



Comfort

- Stabilisation of the foot when walking
- Shock-absorbing heel to relieve joint strain
- Padded tongue to reduce pressure points in the lacing area
- Padded collar for comfort and ankle support
- Ergonomically designed footwear for comfortable wear



Performance

- Sole designed to withstand contact heat up to 300°C

Certifications and norms



EN ISO 20345

S3S HRO CI HI WPA FO A E SC LG SR

Applications

- Agriculture
- Public works
- Building
- Finishing works / Craftsmanship
- Heavy industry
- Light industry

Protects against risks



Antistatic



Heat



Shock



Cold



ARENAL S3S SR

UTILITIES

Robust and comfortable low-cut shoe, adapted to more difficult environments.

Foot protection

Standards - Details

Technical details

Shoe type	Low shoe
Outsole material	PU, Nitrile rubber
Anti-perforation insert	Metal free
Upper material	Leather
Upper finition material	Nubuck
Safety toe-cap	Composite
Lining material	Mesh
Footbed material	PU, Synthetic
Footbed caracteristic	Removable, Perforated, Breathable
Outsole finition	Injected
Weight (g per shoe)	730
Size range	38 → 48



ARENAL S3S SR

UTILITIES

Robust and comfortable low-cut shoe, adapted to more difficult environments.

Safety footwear

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
ARENAS3SNO38	Black	38	ARENAL S3S SR	3295249303532	13295249303539	5	1	8.4 kg	36.2 cm	61.8 cm	28.2 cm
ARENAS3SNO39	Black	39	ARENAL S3S SR	3295249303655	13295249303652	5	1	8.6 kg	27.8 cm	61.4 cm	34.8 cm
ARENAS3SNO40	Black	40	ARENAL S3S SR	3295249303662	13295249303669	5	1	8.8 kg	28.4 cm	62.2 cm	35.8 cm
ARENAS3SNO41	Black	41	ARENAL S3S SR	3295249303679	13295249303676	5	1	9.0 kg	28.8 cm	62.4 cm	35.8 cm
ARENAS3SNO42	Black	42	ARENAL S3S SR	3295249303686	13295249303683	5	1	9.4 kg	28.8 cm	62.4 cm	35.8 cm
ARENAS3SNO43	Black	43	ARENAL S3S SR	3295249303693	13295249303690	5	1	9.9 kg	38.8 cm	67.6 cm	29.8 cm
ARENAS3SNO44	Black	44	ARENAL S3S SR	3295249303709	13295249303706	5	1	10.2 kg	39.0 cm	67.8 cm	29.4 cm
ARENAS3SNO45	Black	45	ARENAL S3S SR	3295249303716	13295249303713	5	1	10.6 kg	39.8 cm	68.2 cm	29.6 cm
ARENAS3SNO46	Black	46	ARENAL S3S SR	3295249303723	13295249303720	5	1	10.7 kg	39.0 cm	67.6 cm	29.8 cm
ARENAS3SNO47	Black	47	ARENAL S3S SR	3295249303730	13295249303737	5	1	11.3 kg	38.4 cm	67.4 cm	29.6 cm
ARENAS3SNO48	Black	48	ARENAL S3S SR	3295249303747	13295249303744	5	1	11.5 kg	38.8 cm	68.0 cm	31.2 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height