



PRODUCT-DETAILS

MJS6-60B

MJS6-60B Joystick



360°

General Information

Extended Product Type	MJS6-60B
Product ID	1SFA611706R6006
EAN	7320500375747
Catalog Description	MJS6-60B Joystick

Long Description

The MJS6-60B Joystick is: 4-position -Momentary Joystick without latching function - Black - Non-illuminated - Chrome Metal - No contact block

This Joystick is part of ABB's modular plastic range, the most versatile range with a high level of flexibility and market-leading electrical ratings. Engineered for total reliability, longer lifetime, and highest mechanical durability. Self-cleaning contacts ensure reliable operation without the need for maintenance, increasing uptime. A high degree of protection guarantees reliability in extreme environments. The innovative design simplifies the entire process, from selection to easy and quick, tool-free installation. The perfect solution for every application.

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85369001

Popular Downloads

Data Sheet, Technical Information	1SFC151007C02__
Instructions and Manuals	1SFC151011M0201

Dimensions

Product Net Width	0.04 m
Product Net Height	0.043 m
Product Net Depth / Length	0.097 m
Product Net Weight	0.062 kg

Technical

Ambient Air Temperature	Operation -25 ... +70 °C Storage -40 ... +85 °C
Color	Black
Actuator Type	Joystick without latching function
Bezel Material	Metal
Illumination	Non-illuminated
Function	Momentary
Sub-Function	4-position
Enclosure Type NEMA	Type1 Type12 Type13 Type4 Type4X
Mechanical Durability	0.5 million

Environmental

Degree of Protection	Front IP66 Front IP67 Front IP69K
----------------------	---

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2022-006479
RoHS Declaration	2CMT2022-006498
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006523
WEEE Category	Product Not in WEEE Scope

Certificates and Declarations

cULus Certificate	9AKK107046A9925
Declaration of Conformity - CE	2CMT2015-005452

Declaration of
Conformity - UKCA

2CMT2020-006121

DNV GL Certificate

E-14107

Container Information

Package Level 1 Units	bag 1 piece
Package Level 1 Width	0.11 m
Package Level 1 Depth / Length	0.15 m
Package Level 1 Height	0.048 m
Package Level 1 Gross Weight	0.065 kg
Package Level 1 EAN	7320500375747

External Classifications and Standards

Object Classification Code	S
ETIM 6	EC000632 - Control switch, Joystick
ETIM 7	EC000632 - Control switch, Joystick
ETIM 8	EC000632 - Control switch, Joystick
eClass	V11.0 : 27371404
UNSPSC	39122227
IDEA Granular Category Code (IGCC)	5280 >> Joystick switch or control
E-Number (Finland)	2312115
E-Number (Norway)	4372968
E-Number (Sweden)	3705021

Categories

Low Voltage Products and Systems → Control Products → Pilot Devices → Modular Plastic Range → MJS Joysticks

