

CT46 - CT Impact D18 Nitrile Sandy Glove

Collection: Impact protection

Range: Hand Protection

Materials: DyUltra™, Nylon, PVC, Elastic, Elastane

Dipping:

Outer Carton: 72

Product information

Introducing our cut D 18 gauge impact glove, designed to provide unrivalled impact protection. Engineered for low-energy impact situations, it safeguards against potential hazards. With its Level D cut resistance, this glove offers reliable protection without compromising dexterity. Experience seamless interaction with touchscreen devices, as it offers full compatibility. The nitrile foam coating ensures exceptional grip in wet and dry conditions. Redefining comfort, this glove is expertly manufactured without glass and steel fibres, minimising skin irritation.

Impact protection

Hand injury is one of the most common and frequent complaints in the workplace. This collection of gloves provides vital protection against impact to the hand from multiple hazards.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 5

EN 388: 2016 + A1: 2018 (3X42DP)

EN 407: 2020 (X1XXXX)

ANSI/ISEA 105: 2016 CUT Level (A4)

ANSI/ISEA 138: 2019 (LEVEL 2)



Features

- Level D cut resistance
- This glove can be used with most mobile touchscreen devices
- Nitrile foam coating for excellent grip in wet and dry conditions
- Free from glass and steel fibres to reduce skin irritation
- For low-energy impact protection
- Retains cut performance level for up to 10 washes
- 18 gauge liner provides excellent comfort, freedom of movement and superb tactile ability
- CE certified
- UKCA marked
- New style
- Retail tag which aids presentation for retail sales



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

CT46 - CT Impact D18 Nitrile Sandy Glove Commodity Code: 6116102091

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
Bracetown Business Park
D15 YN2P, Ireland
Cert No: 2777/25632-01/E00-00

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
CT46G8RXS	Grey/Black	55.0	35.0	27.0	0.1530	0.0520	5036108411726	15036108897244
CT46G8RS	Grey/Black	55.0	35.0	27.0	0.1550	0.0520	5036108411702	15036108897220
CT46G8RM	Grey/Black	55.0	35.0	27.0	0.1740	0.0520	5036108411696	15036108897213
CT46G8RL	Grey/Black	55.0	35.0	27.0	0.1790	0.0520	5036108411689	15036108897206
CT46G8RXL	Grey/Black	55.0	35.0	27.0	0.2000	0.0520	5036108411719	15036108897237
CT46G8RXXL	Grey/Black	55.0	35.0	27.0	0.2030	0.0520	5036108411733	15036108897251