


# Enterprise Networks Cable




KRONE

011110101111000000  
 000001111010101110  
 000011110101011100  
 000111101010111000  
 001111010101110000  
 011110101011100000  
 000001111010101110  
 000011110101011100

TrueNet™ Truly revolutionary

### TRUENET™ C6T


TrueNet™ Category 6 Horizontal PVC solid cable. Ultimate performance, finely tuned to impedance match KRONE jacks. For information on our LSZH range, please contact our sales office.



| Description                            | KRONE Product No. |
|----------------------------------------|-------------------|
| UTP 4pr Cat 6                          | TN6TR-XXRB        |
| UTP 2x4pr Cat 6 Side by Side Web cable | D4T64T6-XX02      |

### TRUENET™ C5ET HORIZONTAL CABLE


TrueNet™ Category 5e Horizontal PVC solid cable. Finely tuned to impedance match KRONE jacks. For information on our LSZH range, please contact our sales office.



| Description                                    | KRONE Product No. |
|------------------------------------------------|-------------------|
| UTP 4pr 24 AWG Cat 5e                          | TN5ETR-XXRB       |
| UTP 2x4pr 24 AWG Cat 5e Side by Side Web cable | D4T54T5-XX02      |

### UTP CAT5E 4 PAIR

KRONE standard cable is used for high speed data transmissions for LAN's, it will support Gigabit IEEE 802.3, IEEE 802.5 Token Ring, ATM 155 and others. Exceeds Category 5e requirements, giving a stable and outstanding performance.




UTP Cat5e 4 Pair

| Description                      | Sheath | Colour | Part No.   |
|----------------------------------|--------|--------|------------|
| UTP 4pr Cat5e (750m Reel)        | PVC    | Grey   | SC5EV-GY05 |
| UTP 4pr Cat5e (1.5km Reel)       | PVC    | Grey   | SC5EV-GY10 |
| UTP 4pr Cat5e (Reelex II - 305m) | PVC    | Grey   | SC5EV-GYII |
| UTP 4pr Cat5e (750m Reel)        | LSZH   | Orange | SC5EL-OR05 |
| UTP 4pr Cat5e (1.5km Reel)       | LSZH   | Orange | SC5EL-OR10 |
| UTP 4pr Cat5e (Reelex II - 305m) | LSZH   | Orange | SC5EL-ORII |

### FTP CAT5E 4 PAIR

KRONE standard cable with overall foil screen is used for high speed data transmissions for LAN's, it will support IEEE 802.3 Gigabit, IEEE 802.5 Token Ring, ATM 155 and others. Exceeds Category 5e requirements, giving a stable and outstanding performance.




FTP Cat5e 4 Pair

| Description                      | Sheath | Colour | Part No.   |
|----------------------------------|--------|--------|------------|
| FTP 4pr Cat5e (Reelex II - 305m) | PVC    | Grey   | SC5EF-GYII |
| FTP 4pr Cat5e (Reelex II - 305m) | LSZH   | Orange | SC5EH-ORII |

### STP CAT5E 4 PAIR

KRONE standard cable with overall foil and braid screen is used for high speed data transmissions for LAN's. It will support Gigabit IEEE 802.3, IEEE 802.5 TokenRing, ATM 155 and others. Exceeds Category 5e requirements, giving a stable and outstanding performance.




STP Cat5e 4 Pair

| Description                      | Sheath | Colour | Part No.   |
|----------------------------------|--------|--------|------------|
| STP 4pr Cat5e (Reelex II - 305m) | PVC    | Grey   | SC5ES-GYII |
| STP 4pr Cat5e (Reelex II - 305m) | LSZH   | Orange | SC5EZ-ORII |

## TWIN UTP CAT5E

KRONE standard cable is used for high speed data transmissions for LAN's. Shot gun construction for multiple ease of installation. It will support Gigabit IEEE 802.3, IEEE 802.5 Token Ring, ATM 155 and others. Exceeds Category 5e requirements, giving a stable and outstanding performance.




Twin UTP Cat5e

| Description                          | Sheath | Colour | Part No.   |
|--------------------------------------|--------|--------|------------|
| UTP 2 x 4pr Cat5e (Reelex II - 305m) | PVC    | Grey   | SC5ET-GYII |
| UTP 2 x 4pr Cat5e (Reelex II - 305m) | LSZH   | Orange | SC5EW-ORII |

## JUMPER WIRE CAT5E

KRONE jumper wire is used at cross connects for IDC Highband modules.




Jumper Wire Cat5e

| Description                    | Sheath | Colour | Part No.  |
|--------------------------------|--------|--------|-----------|
| Jumper wire (Reelex II - 305m) | PVC    | n/a    | SC5e-NSXX |

## UTP CAT6 4 PAIR

KRONE standard cable is used for high speed data transmissions for LAN's, this product gives you maximum future proofing of your passive structured cabling system, it will easily support IEEE 802.3 Gigabit, IEEE 802.5 Token Ring, ATM 155 and others. Exceeds draft Category 6 requirements.




UTP Cat6 4 Pair

| Description                     | Sheath | Colour | Part No.  |
|---------------------------------|--------|--------|-----------|
| UTP 4pr Cat6 (Reelex II - 305m) | PVC    | Grey   | SC6V-GYII |
| UTP 4pr Cat6 (750m Reel)        | PVC    | Grey   | SC6V-GY05 |
| UTP 4pr Cat6 (1.5km Reel)       | PVC    | Grey   | SC6V-GY10 |
| UTP 4pr Cat6 (Reelex II - 305m) | LSZH   | Orange | SC6L-ORII |
| UTP 4pr Cat6 (750m Reel)        | LSZH   | Orange | SC6L-OR05 |
| UTP 4pr Cat6 (1.5km Reel)       | LSZH   | Orange | SC6L-OR10 |



## FTP CAT6 4 PAIR

KRONE standard cable with overall foil screen is used for high speed data transmissions for LAN's, it exceeds the current draft standards of Cat6, which future proofs your network. This will support and exceed the requirements for delivering IEEE 802.3 Gigabit, IEEE 802.5 Token Ring, ATM 155 and others.




FTP Cat6 4 Pair

| Description                     | Sheath | Colour | Part No.  |
|---------------------------------|--------|--------|-----------|
| FTP 4pr Cat6 (Reelex II - 305m) | PVC    | Grey   | SC6F-GYII |
| FTP 4pr Cat6 (1.5km Reel)       | PVC    | Grey   | SC6F-GY10 |
| FTP 4pr Cat6 (Reelex II - 305m) | LSZH   | Orange | SC6H-ORII |
| FTP 4pr Cat6 (1.5km Reel)       | LSZH   | Orange | SC6H-OR10 |

## STP CAT6 4 PAIR

KRONE standard cable with overall foil and braid screen is used for high speed data transmissions for LAN's. It exceeds draft category 6 requirements. This product gives you maximum future proofing of your passive structured cabling system, it will easily support IEEE 802.3 Gigabit, IEEE 802.5 Token Ring, ATM 155 and others.




STP Cat6 4 Pair

| Description                     | Sheath | Colour | Part No.  |
|---------------------------------|--------|--------|-----------|
| STP 4pr Cat6 (Reelex II - 305m) | PVC    | Grey   | SC6S-GYII |
| STP 4pr Cat6 (1.5km Reel)       | PVC    | Grey   | SC6S-GY10 |
| STP 4pr Cat6 (Reelex II - 305m) | LSZH   | Orange | SC6Z-ORII |
| STP 4pr Cat6 (1.5km Reel)       | LSZH   | Orange | SC6Z-OR10 |

## COMBI CABLE (FIBRE & TWIN UTP CAT5E)

A unique product construction allowing both Copper and Fibre to be installed with one cable. Combi cable contains two UTP Cat5e 4 pair cables with a central divide that can carry both multimode and singlemode fibre. Please contact our sales office for more information.




Combi Cable (Fibre & UTP Cat5e)

| Description                                         | Sheath | Colour | Part No.  |
|-----------------------------------------------------|--------|--------|-----------|
| UTP 2x4pr Cat5e with MM/SM Fibre (Reelex II - 305m) | PVC    | Grey   | SCBX-GY11 |
| UTP 2x4pr Cat5e with MM/SM Fibre (750m Reel)        | PVC    | Grey   | SCBX-GY05 |
| UTP 2x4pr Cat5e with MM/SM Fibre (1.5km Reel)       | PVC    | Grey   | SCBX-GY10 |
| UTP 2x4pr Cat5e with MM/SM Fibre (Reelex II - 305m) | LSZH   | Orange | SCBX-OR11 |
| UTP 2x4pr Cat5e with MM/SM Fibre (750m Reel)        | LSZH   | Orange | SCBX-OR05 |
| UTP 2x4pr Cat5e with MM/SM Fibre (1.5km Reel)       | LSZH   | Orange | SCBX-OR10 |

## UTP CAT5E 25 PAIR

Multipair voice and data cable.



| Description                   | Sheath | Colour | KRONE Product No. |
|-------------------------------|--------|--------|-------------------|
| UTP Cat5 25 pair (Reelex II)  | PVC    | Grey   | SC5eA-GYII        |
| UTP Cat5 25 pair (750m)       | PVC    | Grey   | SC5eA-GY05        |
| UTP Cat5 25 pair (1.5km Reel) | PVC    | Grey   | SC5eA-GY10        |


## UTP CAT3 25-600 PAIR

Multipair voice and data cable.

| Description       | Sheath | Colour | KRONE Product No. |
|-------------------|--------|--------|-------------------|
| UTP Cat3 25 pair  | PVC    | Grey   | SC3aA-GYXX        |
| UTP Cat3 100 pair | PVC    | Grey   | SC3aD-GYXX        |
| UTP Cat3 600 pair | PVC    | Grey   | SC3aB-GYXX        |

## SIMPLEX INDOOR

2.8mm diameter multimode and singlemode patchcord cable.




Simplex indoor fibre cable

| Description         | KRONE Product No.   |
|---------------------|---------------------|
| 50/125µm            | 7001ZHSSFH05028SP   |
| 50/125µm enhanced   | 7001ZHSSFH05028HISP |
| 62.5/125µm          | 7001ZHSSFH06228SP   |
| 62.5/125µm enhanced | 7001ZHSSFH06228HISP |
| 9/125µm             | 7001ZHSSFH01028SP   |

## DUPLEX INDOOR

2.8mm Zip duplex multimode and singlemode patchcord cable.




Duplex indoor fibre cable

| Description         | KRONE Product No. |
|---------------------|-------------------|
| 50/125µm            | 7002ZHSZCH05028   |
| 50/125µm enhanced   | 7002ZHSZCH05028HI |
| 62.5/125µm          | 7002ZHSZCH06228   |
| 62.5/125µm enhanced | 7002ZHSZCH0628HI  |
| 9/125µm             | 7002ZHSZCH01028   |

## TIGHT BUFFERED FIBRE CABLE

4, 8, 12, 16 or 24 fibre multimode and singlemode distribution cable.  
Tight buffered, internal/external grade.




Tight buffered fibre distribution cable


| Description         | 4 Fibre         | 8 Fibre         | 12 Fibre        | 16 Fibre        | 24 Fibre        |
|---------------------|-----------------|-----------------|-----------------|-----------------|-----------------|
| 50/125µm            | 5004LZHIOC050   | 5008LZHIOC050   | 5012LZHIOC050   | 5016LZHIOC050   | 5024LZHIOC050   |
| 50/125µm enhanced   | 5004LZHIOC050HI | 5008LZHIOC050HI | 5012LZHIOC050HI | 5016LZHIOC050HI | 5024LZHIOC050HI |
| 62.5/125µm          | 7004LZHIOC062   | 7008LZHIOC062   | 7012LZHIOC062   | 7016LZHIOC062   | 7024LZHIOC062   |
| 62.5/125µm enhanced | 7004LZHIOC062HI | 7008LZHIOC062HI | 7012LZHIOC062HI | 7016LZHIOC062HI | 7024LZHIOC062HI |
| 9/125µm             | 7004ZHSIOC010   | 7008ZHSIOC010   | 7012ZHSIOC010   | 7016ZHSIOC010   | 7024ZHSIOC010   |

## LOOSE TUBE FIBRE CABLE

4, 8, 12, 16 or 24 fibre multimode and singlemode distribution cable.  
Loose tube, internal/external grade.



Loose tube up to 12 fibres



Loose tube up to 48 fibres

| Description         | 4 Fibre       | 8 Fibre       | 12 Fibre      | 16 Fibre      | 24 Fibre      |
|---------------------|---------------|---------------|---------------|---------------|---------------|
| 50/125µm            | 7023/3/222/04 | 7023/3/222/08 | 7023/3/222/12 | 7023/3/222/16 | 7023/3/222/24 |
| 50/125µm enhanced   | 7023/3/223/04 | 7023/3/223/08 | 7023/3/223/12 | 7023/3/223/16 | 7023/3/223/24 |
| 62.5/125µm          | 7023/3/220/04 | 7023/3/220/08 | 7023/3/220/12 | 7023/3/220/16 | 7023/3/220/24 |
| 62.5/125µm enhanced | 7023/3/221/04 | 7023/3/221/08 | 7023/3/221/12 | 7023/3/221/16 | 7023/3/221/24 |
| 9/125µm             | 7023/3/224/04 | 7023/3/224/08 | 7023/3/224/12 | 7023/3/224/16 | 7023/3/224/24 |