

Features

- ESD – Designed to safely discharge static electricity and protect electronic components from electrostatic discharge events.
- Wheeled
- Height Adjustable
- Back Adjustable
- Seat Adjustable
- Available in different sizes

RS PRO ESD PU Comfort

RS Stock No.: 0665652



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The Comfort ESD Chair is a practical solution for environments where electrostatic protection is essential and long-term use is expected. Its ergonomic design and high-quality construction provide comfort and safety throughout the working day.

Product Features:

- ✓ **Soft ESD-safe surface** – ensures user comfort and helps safely discharge static electricity
- ✓ **Adjustable seat height, seat depth, and backrest height** – allows for personalized adjustment to individual needs
- ✓ **Sturdy aluminum five-star base** – offers excellent stability and long-lasting durability
- ✓ **Conductive castors** – rubber-coated to protect floors and maintain effective ESD control
- ✓ **Easy-to-clean surface** – resists dirt and wear, simplifying daily maintenance
- ✓ **Ergonomically shaped seat and backrest** – support a natural sitting posture and enhance comfort during extended use

Applications:

The Comfort ESD Chair is well-suited for service centers, production areas, and other environments where ESD control is a priority. Its ergonomic construction and durable materials make it a reliable choice for daily use across industries such as electronics, automotive, general manufacturing, medical, pharmaceutical, and defense.

General Specifications

TOTAL HEIGHT (mm)	720-925
TOTAL WIDTH (mm)	660
WEIGHT (kg)	10,8
MAX LOAD CAPACITY (kg)	120 (up to 200 kg with a special gas lift)
HEIGHT ADJUSTMENT RANGE (mm)	430-560mm
SEAT DIMENSIONS (mm)	450 x 440
BACKREST DIMENSIONS (mm)	310 x 400
ESD	YES
COLOUR	BLACK
MATERIAL	POLYURETHANE
BASE MATERIAL	ALUMINIUM
CASTORS	CONDUCTIVE, RUBBER-COATED TO PREVENT SCRATCHING
RESISTANCE GROUNDING (Ohm)	$10^6 - 10^8$

Approvals

Chair compliance with standards	PN-EN IEC 61340-5-1:2025-02, PN-EN 1335-1:2004, PN-EN 1335-2:2009, PN-EN 1335-3:2009, PN-EN 1022:2007
---------------------------------	---

Similar Products

Stock No.	Brand	Product Name
0665653	RS PRO	ESD PU Comfort chair, seat height adjustment 510-700mm
0665654	RS PRO	ESD PU Comfort chair, seat height adjustment 550-800mm
0665638	RS PRO	ESD PU chair, seat height adjustment 440-570mm
0665639	RS PRO	ESD PU chair, seat height adjustment 525-710mm
0665640	RS PRO	ESD PU chair, seat height adjustment 580-830mm

Accessories

Stock No.	Brand	Product Name
0665661	RS PRO	ESD castor, grey rubber tyre, diameter 50mm (**brake option available on request**)
0665662	RS PRO	ESD metal castor, diameter 50mm
0665664	RS PRO	ESD glides
0665665	RS PRO	ESD footrest
0665666	RS PRO	ESD PU armrests
		armrests, black steel + antistatic PU cover
		armrests with height adjustment, black steel + antistatic PU covers

Electrical Specifications