



ALPHA 400 DIN spare part door, door half, right H = 1250 mm, W = 275 mm IP43, IP44, IP55, RAL 9016, protection class 1 and 2 including rotary handle

| Model                               |  |                      |             |
|-------------------------------------|--|----------------------|-------------|
| product brand name                  |  | ALPHA                |             |
| product designation                 |  | Door half            |             |
| design of the product               |  | Closed               |             |
| design of the surface               |  | Powder-coated        |             |
| design of the product EMC version   |  | No                   |             |
| Protection class                    |  |                      |             |
| protection class IP                 |  | IP55                 |             |
| operating resource protection class |  | Safety class 1 and 2 |             |
| Appearance                          |  |                      |             |
| RAL color number                    |  | 9016                 |             |
| color                               |  | Traffic white        |             |
| Product details                     |  |                      |             |
| product component                   |  |                      |             |
| • ventilation                       |  | No                   |             |
| • viewing door                      |  | No                   |             |
| • door for disconnecter lock        |  | No                   |             |
| accessories included                |  | incl. rotary handle  |             |
| Mechanical Design                   |  |                      |             |
| height                              |  | 1 250 mm             |             |
| width                               |  | 275 mm               |             |
| opening direction of the door       |  | right                |             |
| net weight                          |  | 4 kg                 |             |
| material                            |  | steel                |             |
| Approvals Certificates              |  |                      |             |
| General Product Approval            |  | Test Certificates    | other       |
|                                     |  |                      | Environment |



[Special Test Certificate](#)

[Confirmation](#)

[Miscellaneous](#)

[Environmental Confirmations](#)

Environment

[Environmental Confirmations](#)

#### Further information

##### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8GK9510-8KK32>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8GK9510-8KK32>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK9510-8KK32](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK9510-8KK32)

##### CAX-Online-Generator

<http://www.siemens.com/cax>

##### Tender specifications

<http://www.siemens.com/specifications>



last modified:

5/24/2025 

