



Halogen Classic Candle B35

Halogen Classic 42W E14 240V B35 1CT

Philips Halogen Classic Candle light bulbs offer the classical shape you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

Product data

• General Characteristics

Cap-Base	SES
Bulb	B35 [B 35mm]
Bulb Finish	Clear
Burning Position	any [Any/Universal]
Nominal Lifetime	2000 hr
Rated Lifetime	2000 hr
Rated Lifetime (years)	2 an

• Light Technical Characteristics

Colour Rendering Index	100 Ra8
Colour Temperature	2800 K
Colour Temperature Technical	2800 K
Lamp Luminous Flux	630 Lm
Rated Luminous Flux	630 Lm
Lamp Luminous Efficacy	15.0 Lm/W
LLMF - end nominal lifetime	80 (min) %

• Electrical Characteristics

Rated Wattage	42.0 W
Lamp Wattage	42 W
Technical Lamp Power	42 W
Power Factor	1 -
Voltage	240 V
Lamp Current	0.18 A
Dimmable	yes
Wattage Equivalent	55 W
Starting Time	0.0 s

Warm-up Time to 60% Light Outp	instant full light
--------------------------------	--------------------

• Environmental Characteristics

Energy Efficiency Label (EEL)	D
Energy consumption kWh/1000h	42 kWh

• Measuring Conditions

Switching cycle	8000X
-----------------	-------

• Luminaire Design Requirements

Cap-Base Temperature	130 (max) C
----------------------	-------------

• Product Dimensions

Overall Length C	99.2 (max) mm
Diameter D	36 (max) mm

• Product Data

Order code	820621 02
Full product code	872790082062102
Full product name	Halogen Classic 42W E14 240V B35 1CT
Order product name	Halogen Classic 42W E14 240V B35 1CT/15
Pieces per pack	1
Packing configuration	15
Packs per outerbox	15
Bar code on pack - EAN1	8727900820621


PHILIPS

Halogen Classic Candle B35

Bar code on
outerbox - EAN3 8718696462430
Logistic code(s) -
12NC 925646345505


Net weight per piece 18.100 gr

Dimensional drawing



Halogen Classic 42W E14 240V B35 1CT

Product	C (Max)	D (Max)
HalClass 42W E14 240V B35 CL	99.2	36



E14



© 2015 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2015, September 24
data subject to change