


Series 7400 Krafftform ESD adjustable torque screwdrivers (0.1-3.0 Nm) with Rapidaptor quick-release chuck, art. no. 7430 ESD x 0.10-0.34 N m
ESD Series



EAN:	4013288179159	Size:	155x37x37 mm
Part number:	05074780001	Weight:	122 g
Article number:	7400 ESD	Country of origin:	CZ
		Customs tariff number:	82054000



- Adjustable Krafftform ESD torque screwdriver with Rapidaptor quick-release chuck
- ESD-safe tool thanks to surface resistance of $< 10^9$ Ohm
- Multi-component Krafftform Micro handle for fast and ergonomic screwdriving
- Hexagonal anti-roll feature against rolling away
- Rapidaptor quick-release chuck for bits with 1/4" hex head drive

Wera torque screwdriver. Dependable protection against electrostatic energy and associated damage. Variable torque setting option with highest precision. Simple adjustment of the required torque value without any special tools. Easy-to-read scale value. Rapidaptor quick-release technology for rapid bit change. Unlimited torque to loosen seized screws. Multi-component Krafftform handle with hard and soft zones for high working speeds, whilst being easy on the hand. Suitable for bits with 1/4" hexagon head drive as per DIN ISO 1173-C 6.3 and E 6.3 (ISO 1173).

Web link

https://products.wera.de/en/torque_tools_series_7400_krafftform_torque_screwdrivers_variable_torque_adjustment_models_7400_esd.html

Wera - 7400 ESD
05074780001 - 4013288179159

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Series 7400 Kraftform ESD adjustable torque screwdrivers (0.1-3.0 Nm) with Rapidaptor quick-release chuck, art. no. 7430 ESD x 0.10-0.34 N m ESD Series



Adjustable Torque Screwdrivers

Wera ESD Tools

Simple setting

Easy-to-read



Wera's adjustable torque screwdrivers allow variable torque settings with maximum precision and ensure that the user gets the very best results in the familiar Wera design with superior ergonomics.

The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.

Simple setting of the required torque by hand.

Easy-to-read scale value.

Attachable magnifying glass

Measurement accuracy

Unlimited torque

Versatile



Articles 7430, 7431 and 7432 all come with a magnifying glass. This can be easily attached on to the scale, dramatically improving visibility.

Measurement accuracy is $\pm 6\%$ in accordance with the standard DIN EN ISO 6789. Distinctly audible and noticeable excess-load signal when the pre-set torque is reached.

Unlimited torque for loosening seized screws.

Rapidaptor technology makes the tool adaptable since bits and sockets can be exchanged rapidly.

Web link

https://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_variable_torque_adjustment_models_7400_esd.html







Wera - 7400 ESD
05074780001 - 4013288179159

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Series 7400 Kraftform ESD adjustable torque screwdrivers (0.1-3.0 Nm) with Rapidaptor quick-release chuck, art. no. 7430 ESD x 0.10-0.34 N m
ESD Series



Further versions in this product family:

								
	art. no.	mm	inch	Nm	Nm	mm	inch	
	05074780001¹⁾	7430 ESD	89	1/4	0.10-0.34	0.015	142	5 7/16
	05074782001 ¹⁾	7431 ESD	89	1/4	0.30-1.00	0.05	142	5 7/16
	05074784001 ¹⁾	7432 ESD	89	1/4	0.90-1.50	0.05	142	5 7/16
	05074730001	7440 ESD	105	1/4	0.3-1.2	0.05	155	6
	05074731001	7441 ESD	105	1/4	1.2-3.0	0.10	155	6

1) With attachable magnifying glass, dramatically improving visibility.

Web link

https://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_variable_torque_adjustment_models_7400_esd.html

Wera - 7400 ESD
05074780001 - 4013288179159

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de