




AH 3140

Popular item

Withdrawal sleeves

Technical specification



DIMENSIONS

d_1	190 mm
d	200 mm
B_1	134 mm
B_2	140 mm
G	Tr 220x4
G_1	21 mm

MASS

Mass withdrawal sleeve	5.65 kg
------------------------	---------

ASSOCIATED PRODUCTS

Hydraulic nut	HMV 44 E
Nut for removal	HM 3044

More information

<p data-bbox="134 331 331 365">Product details</p> <p data-bbox="146 412 376 445">Designs and variants</p> <hr data-bbox="134 477 691 481"/> <p data-bbox="146 492 290 526">Product data</p> <hr data-bbox="134 557 691 562"/> <p data-bbox="146 573 360 607">Designation system</p> <hr data-bbox="134 638 691 642"/>	<p data-bbox="850 331 922 365">Tools</p> <p data-bbox="863 412 1185 445">Oil Injection Method Program</p> <hr data-bbox="850 477 1407 481"/>
--	--

Terms and conditions

By accessing and using this website / app of SKF Group, meaning AB SKF and / or any of its affiliates ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app. Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service. Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website / app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.