

Tons Five Foam TF-5

Level d cut resistant glove made from recycled polyester with foam nitrile palm

From the TONS range, with very good mechanical resistance & excellent cut protection.

Features

- ▲ Cut resistant: Level D/A4
- ▲ Durable foam nitrile palm coating grips in dry, damp & light oily conditions
- ▲ Excellent dexterity
- ▲ Medium weight feel
- ▲ Breathable materials
- ▲ Knitwrist cuff style
- ▲ RCS (Recycled Claim Standard) certified
- ▲ 1 pair = 1 recycled 500ml PET bottle

26g
CO₂
savings



Certifications



Suitable industries & applications

Industries

- ▲ Automotive
- ▲ Construction
- ▲ Waste and Recycling
- ▲ Highways and Infrastructure
- ▲ Steel and Metals

Applications

- ▲ Component and Product Assembly
- ▲ Electrical Engineering and Maintenance
- ▲ Metal Fabrication Work
- ▲ Woodwork and Fabrication

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

Tons Five Foam TF-5

Level d cut resistant glove made from recycled polyester with foam nitrile palm

Product information

Materials	Liner:	13 Gauge Engineered HPPE, Glass Fibre, Recycled Polyester, HPPE
	Coating:	Foam Nitrile
Colour	Grey / Black	
Length	225mm	
Cuff Style	Elasticated Knit Wrist	

Ordering information

XS	TNS0500	Items per Pack 10 x Pairs
S	TNS0501	
M	TNS0502	
L	TNS0503	Items per Case 120 x Pairs
XL	TNS0504	
XXL	TNS0505	

Additional information

Certification legend



or click [here](#)

Declaration of conformity



or click [here](#)

View product online



or click [here](#)

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM
Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES
Globus Americas LLC, 45 Rockefeller Plaza, Suite 2000, New York City, New York, 10111, USA

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment.
The manufacturer reserves the right to make any modifications it deems necessary.