



Hook tool set

13000-13003/4 250 mm

Product no. 96722803

GTIN 4018754353583

Model 13000-13003/4 250mm



Label.

Hook tool set 4 pcs.

Properties.

- extra long design
- universally usable for assembly and removal of small parts
- high hardness values (50-55 HRC)
- with 3-component handle
- in a sturdy polyester textile case with Velcro fastener
- a compact storage solution to keep your tools safe
- embroidered STAHLWILLE logo

Contains 4-pieces:

4 hook tools No. 13000-13003: straight, 45°; 90°; rounded

Benefits.

4-piece set with extra-long hook tools for assembling/disassembling small parts such as O-rings, seals and trims.

The 250 mm long blades are sturdy, durable and ideal for working in tight spaces.

The practical textile case offers a well-organised storage solution.

The set includes a 90° degree hook, a 45° degree hook, a rounded hook and a straight hook.

Ergonomically shaped 3-component handle enables safe handling, even with oily hands.

Product highlights.



Universal use.

Universally applicable hooks and picks for fitting and removing small components such as simmerring seals and O-rings, seals, trim strip clips and panelling without damaging them. Also indispensable helpers in many other situations.



PRODUCT IMAGE
IN PROGRESS

Extra-long version.

With an extra length of 250 mm, these hook tools are indispensable helpers in confined spaces and for difficult connections. Thanks to their special design, they can be used, for example, for work on the engine compartment, on the bodywork or for wiring, offering optimal leverage for more power.



PRODUCT IMAGE
IN PROGRESS

High quality and durable.

The tool is made of high-quality steel, which gives it outstanding stability and resistance to continuous use.



PRODUCT IMAGE
IN PROGRESS

Expert composition.

The set is stored in a practical textile bag with a Velcro closure. This makes it convenient, space-saving and safe to transport anywhere.

Technologies and features.



3-component handle

Our 3-component handle combines hard, soft and special fibre-coated components, which give it its optimised ergonomics, maximum power transmission, and increased safety during daily use.

Technical attributes.

Number of tools

4 pcs.

Logistics data.

Depth mm (IFS)	280
Width mm (IFS)	60
Height mm (IFS)	25
WEEE/ElektroG	nicht ear-pflichtig
Length (packed, mm)	280
Width (packed, mm)	60
Height (packed, mm)	25

Volume (packed, dm3)	0.42 dm3
Art. no.	96722803
Weight (gross, kg)	0,326
Weight PAP (kg)	0,000
Weight PVC (kg)	0,004
GTIN	4018754353583
Country of origin AWR	CHINA
Region of origin	Ausländischer Ursprung
Customs tariff no.	82055980
Packing standard	1
Weight	174 g

Variants.

Art. no.	Model no. (ERP)	Description	GTIN
96722803	13000-13003/4 250mm	Hook tool set 4 pcs.	4018754353583

GTIN.



Images.





STAHLWILLE Eduard Wille GmbH & Co. KG

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0 · Fax: +49 202 4791-393

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH & Co. KG, Wuppertal