

CHROME

BUSSOLE E ACCESSORI CHROME
CHROME sockets and accessories



Realizzate in acciaio al Cromo Vanadio di alta qualità. Collare godronato per una miglior presa e resistente rivestimento superficiale di cromatura.

Made in high quality Chrome-Vanadium steel. Knurled collar for better grip and resistant chrome-plated surface coating.



Impronta esagonale tipo SUPER- LOCK: il contatto con il dado non avviene sullo spigolo ma sulla faccia dell'esagono, che offre una maggior superficie di appoggio.

SUPER-LOCK hex tip: the contact with the nut does not take place on the edge, but on the face of the hexagon, which offers a larger support surface.




Indicate per applicazioni manuali in ambito professionale.

Suitable for professional manual applications.

64224

BARRE A "T"

LEVA PER BUSSOLE CON ASTA MOBILE
LEVER FOR SOCKETS WITH MOBILE ROD



L mm	A/B/C	PCS.	COD.
300	B	1	64224001





SELFPACK
1 pc.

L mm	COD.
300	64224001001

64224

CRICCHETTI REVERSIBILI 72 DENTI

CRICCHETTO REVERSIBILE 72T
72 TREVERSIBLE RATCHET





L mm	A/B/C	PCS.	COD.
250	B	1	64224005


64224

CRICCHETTI REVERSIBILI 45 DENTI

CRICCHETTO REVERSIBILE 45T
45T REVERSIBLE RATCHET





L mm	A/B/C	PCS.	COD.
255	B	1	64224006



64224

CRICCHETTI ONE-TOUCH

CRICCHETTO REVERSIBILE SISTEMA ONE-TOUCH
 REVERSIBLE RATCHET ONE-TOUCH SYSTEM



L mm	A/B/C	PCS.	COD.
245	B	1	64224010



FOCUS ON






Movimento a 60 denti, ghiera di inversione della rotazione direttamente sul manico.
 Movement with 60 teeth, reversal of the rotation of the ring nut directly on the handle.

64224

CRICCHETTI TELESCOPICI

CRICCHETTO REVERSIBILE CON ASTA TELESCOPICA
 REVERSIBLE RATCHET WITH TELESCOPIC ROD



L mm	ℓ mm	A/B/C	PCS.	COD.
508	368	B	1	64224015



FOCUS ON



Movimento a 36 denti, testa snodata ad alta resistenza, braccio telescopico.
 Movement with 36 teeth, high-resistance jointed head, telescopic arm.

64224

BARRE A "T" SNODATE

BARRA A T SNODATA PER BUSSOLE 1/2" CON ASTA MOBILE

SLIDING T BAR WITH UNIVERSAL JOINT FOR 1/2" SOCKETS

EASYPACK | sacchetto PVC con Euro-hole - PVC bags with Euro-hole


A



B



C



L mm	A/B/C	PCS.	COD.
495	B	1	64224105