

# KWD RANGE

## KWD205 Rigger Safety Boot - S1P/S1



**KING'S**

by Honeywell

*The Logical Choice*



**Description:** Leather Pull-up Safety Boot

**Size:** UK 3-13 | US 4-14 | EU 36-48

**Application:** Construction, Mining, Manufacturing, Heavy and Light Industries, Utilities, Oil and Gas

**Standard:** SR (EN ISO 20345:2022); S1P/S1



SKU	Steel Midsole	Color	Outsole	Category
KWD205	Yes	Black	Dual Density PU	S1P
KWD205X	No	Black	Dual Density PU	S1
KWD205C	Yes	Brown	Dual Density PU	S1P
KWD205CX	No	Brown	Dual Density PU	S1

### Features:

- Tough 2.0 - 2.2 mm thick full-grain leather upper with good breathability.
- Side pull-up straps for easy donning and doffing even when wearing gloves.
- Stability Torsion Zone offers optimal support for a wide range of foot arch profiles, helping to prevent feet pronation and supination.
- Exceptional shock absorption for elevated comfort and reduced foot fatigue.
- Outsole design engineered to complement the natural biomechanics of the walking gait.
- Wider outsole surface area provides increased contact with ground to enhance stability.
- Enhanced outsole thickness to deliver exceptional cushioning and comfort with every step.
- Strong leather upper and sole bond to withstand demanding work environments.
- Tread with deeper grip patterns and enhanced grip variations offers superior traction and stability.
- King's signature wide profile steel toecap for greater comfort.
- King's Comfort Footbed features ultra-breathable perforated channels for quick drying and all-day feet freshness.
- Highly breathable 3-D lining minimises skin abrasion, keeps feet insulated and effectively wicks away moisture.
- Lightweight, shock absorbing dual density polyurethane (PU) sole for added comfort.
- Wear-off indicators provide an early warning on sole wear and potential loss of grip.
- Excellent slip resistant sole delivers durable traction; SR (EN ISO 20345:2022); Anti-static.
- Sole resistant to mineral and organic oils.

### SOLE FEATURES



Puncture Resistant



Anti-Static



Slip Resistant



Mineral Oils Resistant



Organic Oils & Fats Resistant

### FOOTWEAR FEATURES



2.0 - 2.2mm Full Grain Leather



Wear-off Indicator



Toe Bumper



Steel Safety Toecap

### COMFORT FEATURES



Wide Profile Toecap



Breathable Lining



Comfort Footbed



Impact Absorption



Lightweight



LEARN MORE  
automation.honeywell.com