

8100 SA 14 Zyklop Comfort ratchet set, reversing lever, 1/4" drive, metric, 28 pieces



EAN: 4013288236821
Part number: 05005541001
Article number: 8100 SA 14

Size: 200x115x58 mm
Weight: 823 g
Country of origin: CZ
Customs tariff number: 82041100

- 28-piece Zyklop Comfort ratchet set; 1/4"; sockets in metric sizes
- Zyklop Comfort ratchet with pleasant feel thanks to the plastic sleeve, which also protects surfaces from damage
- Ratchet in extremely slim design; fine toothing with 80 teeth, short return angle of only 4.5° for easy working even in very confined spaces
- Safe socket lock via push button, convenient direction change thanks to the reversing lever
- 1/4" Zyklop wobble extension with swivel angle of 15° in all directions
- One bit holder for 1/4" bits; 15 bits for universal use (Phillips, Pozidriv, TORX®, hexagonal socket)
- Compact textile box with twist-to-unlock system: the tools are securely stored, yet easy to remove
- Textile box made of robust material, protects surfaces from damage, can be docked onto the Wera 2go system

28-piece ratchet set, 1/4", sockets in metric sizes. One Zyklop Comfort ratchet with reversing lever, fine-toothed with 80 teeth, low return angle of only 4.5°; 9 Zyklop sockets with Take it easy tool finder: colour coding by size and extra laser-engraved size indication to find the required tool quickly; one Zyklop extension (150 mm long) with fast-rotating sleeve for fast "spinning", one Wobble extension with pivoting angle of 15° in all directions, one bit adapter (1/4" square head socket to 1/4" hexagonal socket), 15 bits, tough for universal use. One robust textile box, compact design for space-saving tool storage; the firm and light material of the textile box lowers the weight of the set - ideal for mobile use.



Web link
<https://www.wera.de/en/05005541001>

Wera - 8100 SA 14
05005541001 - 4013288236821

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

For small spaces




28-piece Zyklop Comfort ratchet set; 1/4"; sockets in metric sizes




With its extremely slim design, the Zyklop Comfort ratchet allows easy working even in very confined spaces.

Fine-tooth design



With its fine toothing with 80 teeth, the Zyklop Comfort ratchet allows a short return angle of only 4.5°.

Plastic coated



The plastic sleeve makes working comfortable and safe even at extremely low or high temperatures.

Switch lever



Switch lever for convenient change of direction.

Ball lock



The ball lock ensures sockets and accessories fit securely, providing increased safety during operation. A short press on the release button allows the tool to be changed quickly.

Take it easy tool finder system



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

Easy removal of the ratchet



Thanks to the twist-to-unlock system, the ratchet can be easily removed.

8100 SA 14 Zyklus Comfort ratchet set, reversing lever, 1/4" drive, metric, 28 pieces



Set contents:

8010 A Zyklus Comfort ratchet, with reversing lever, with 1/4" drive, 1/4" x 144 mm



05005600001 1x 1/4" x 144 mm



8790 HMA Zyklus 1/4" socket, 5 x 23 mm



05003503001	1x 5 x 23 mm
05003504001	1x 5.5 x 23 mm
05003505001	1x 6 x 23 mm
05003506001	1x 7 x 23 mm
05003507001	1x 8 x 23 mm
05003509001	1x 10 x 23 mm
05003510001	1x 11 x 23 mm
05003511001	1x 12 x 23 mm
05003512001	1x 13 x 23 mm



8794 LA Zyklus extension with free-turning sleeve, long, 1/4", 1/4" x 150 mm



05003526001 1x 1/4" x 150 mm



8794 A Zyklus wobble extension, 1/4", 1/4" x 56 mm



05003527001 1x 1/4" x 56 mm



8784 A1 Zyklus bit adaptor, 1/4", 1/4" x 37 mm



05003529001 1x 1/4" x 37 mm



851/4 TZ bits, PH 1 x 50 mm



05059805001	1x PH 1 x 50 mm
05059810001	1x PH 2 x 50 mm
05059815001	1x PH 3 x 50 mm



855/4 TZ bits, PZ 2 x 50 mm



05060010001	1x PZ 2 x 50 mm
05060015001	1x PZ 3 x 50 mm



867/4 Z TORX® bits, TX 10 x 50 mm



05060132001	1x TX 10 x 50 mm
05060133001	1x TX 15 x 50 mm
05060134001	1x TX 20 x 50 mm
05060135001	1x TX 25 x 50 mm
05060136001	1x TX 27 x 50 mm
05060137001	1x TX 30 x 50 mm



840/4 Z bits, 3 x 50 mm



05059605001	1x 3 x 50 mm
05059610001	1x 4 x 50 mm
05059615001	1x 5 x 50 mm
05059620001 ¹⁾	1x 6 x 50 mm



1) Hexagonal blade

Web link


<https://www.wera.de/en/05005541001>

Wera - 8100 SA 14
05005541001 - 4013288236821

Wera Werkzeuge GmbH
Körzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Hook and Loop Fastener Strip 120, 120 x 50 mm

1x 120 x 50 mm



Web link

<https://www.wera.de/en/05005541001>

Wera - 8100 SA 14
05005541001 - 4013288236821

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de