


▶ **INDOOR/OUTDOOR GRADE VINYL TAPE (B-580)**

- ▶ Labels adhere well to pipes, walls, equipment, windows – most clean, dry surfaces
- ▶ Conforms well to irregular, curved or rough surfaces – it even stands up to grease, oil and most industrial chemicals
- ▶ Five-year average outdoor durability in temperatures from 180°F to -40°F (82°C to -40°C), can be applied as low as 0°F (-18°C)



Size	Part Number													
	White	Clear	Yellow	Green	Red	Blue	Lt. Blue	Orange	Black	Tan	Grey	Brown	Gold	Purple
0.500" x 50' (13 mm x 15.2 m)	42018	42076	42022	42026	42030	42034	—	42038	42042	—	42046	42050	42054	42058
1.000" x 50' (25 mm x 15.2 m)	42019	42077	42023	42027	42031	42035	42133	42039	42043	42135	42047	42051	42055	42059
2.000" x 50' (51 mm x 15.2 m)	42021	42079	42025	42029	42033	42037	42134	42041	42045	42136	42049	42053	42057	42061

▶ **REFLECTIVE TAPE (B-584)**

- ▶ Suitable for indoor or outdoor use
- ▶ Reflective capabilities are ideal for reading labels in low light conditions with a flashlight or from a vehicle
- ▶ Applications include utility pole and box labeling, door labeling, labeling rooftop equipment and equipment that needs to be viewed from a road side



Size	Part Number		
	Reflective White	Reflective Orange	Reflective Yellow
1.000" x 33' (25.0 mm x 10.0 m)	42062	42066	42064
2.000" x 33' (51.0 mm x 10.0 m)	42063	42067	42065

▶ **ECONOMY POLYPROPYLENE TAPE (B-529)**

- ▶ Ideal, low-cost label
- ▶ For use indoors on smooth, flat surfaces
- ▶ Available in three sizes, white only



Size	Part Number
	White
0.500" x 50' (13.0 mm x 15.2 m)	42068
1.000" x 50' (25.0 mm x 15.2 m)	42069
2.000" x 50' (51.0 mm x 15.2 m)	42071

▶ **REPOSITIONABLE VINYL TAPE (B-581)**

- ▶ Vinyl tape has a special adhesive that allows easy removal of label to reapply again... and again
- ▶ Best choice for indoor marking where frequent repositioning is required, such as shelves



Size	Part Number	
	Yellow	White
0.500" x 50' (13.0 mm x 15.2 m)	42103	42100
1.000" x 50' (25.0 mm x 15.2 m)	42104	42101
2.000" x 50' (51.0 mm x 15.2 m)	42105	42102

▶ **TAMPER RESISTANT TAPE (B-530)**

- ▶ Tape destructs into tiny fragments when tampered with, making removal very tedious and difficult
- ▶ White only



Size	Part Number
	White
0.500" x 50' (13.0 mm x 15.2 m)	42137
1.000" x 50' (25.0 mm x 15.2 m)	42138
2.000" x 50' (51.0 mm x 15.2 m)	42139